

GFCI – Ground Fault Circuit Interrupters

Provide personal protection from ground faults and open neutral conditions anywhere electrical equipment is used. All GFCIs are compact, weatherproof/rainproof and engineered to handle rugged conditions of any jobsite. All models feature molded connectors, 12 or 14 gauge OSHA safety yellow cords, heavy-duty strain relief, reinforced blades and pins, manual “Test/Reset” buttons, and industrial grade relays.



Right Angle

Right Angle models offer a variety of receptacles and cord lengths that are perfect where space is at a premium.



02832



03392

PAT NO	LENGTH IN FT	DESCRIPTION	AMP/VOLT/WATT/RATING	RELAY CAPACITY	MASTER PACK	MASTER WT	MASTER PK CUBE
02832	2	12/3 SJTW Tri-Source®	15A 120V/1800W UL/CSA Listed	15A	6	9	.40
02837	25	12/3 SJEOW Tri-Source®	15A 120V/1800W UL/CSA Listed	15A	6	25	1.13
02838	50	12/3 SJEOW Tri-Source®	15A 120V/1800W UL/CSA Listed	15A	6	43	1.41
02839	100	12/3 SJEOW Tri-Source®	15A 120V/1800W UL/CSA Listed	15A	4	52	1.41
03392	2	12/3 SJTW Lighted Tri-Source®	15A 120V/1800W UL/CSA Listed	15A	4	6	.40
02834	2	12/3 SJTW Single Outlet	15A 120V/1800W UL/CSA Listed	15A	6	7	.10

In-Line

In-Line models offer a variety of receptacles with 20A and 30A relay units.



02841

PAT NO	LENGTH IN FT	DESCRIPTION	AMP/VOLT/WATT/RATING	RELAY CAPACITY	MASTER PACK	MASTER WT	MASTER PK CUBE
02841	2.5	12/3 SJTW Tri-Source®	15A 120V/1800W UL/CSA Listed	20A	6	6	.63
02851	2.5	12/3 SEOW Tri-Source® Extra Heavy-Duty	15A 120V/1800W UL Listed	30A	6	8	.63

Duplex Boxes

High impact resin with a slant-roof design to prevent water entry. Receptacles can accommodate large plugs.




02822

PAT NO	LENGTH IN FT	DESCRIPTION	AMP/VOLT/WATT/RATING	RELAY CAPACITY	MASTER PACK	MASTER WT	MASTER PK CUBE
02822	6	12/3 SJTW GFCI w test/reset buttons	15A 120V/1800W UL Listed	25A	6	15	.93
02827	25	14/3 SJEOW GFCI w test/reset buttons	15A 120V/1800W UL Listed	25A	1	3	.26
02828	50	14/3 SJEOW GFCI w test/reset buttons	15A 120V/1800W UL Listed	25A	1	5	.36

Quad Boxes

High impact resin with a slant-roof design to prevent water entry. Receptacles can accommodate large plugs.



02821

PAT NO	LENGTH IN FT	DESCRIPTION	AMP/VOLT/WATT/RATING	RELAY CAPACITY	MASTER PACK	MASTER WT	MASTER PK CUBE
02816	6	12/3 SJTW GFCI w handle, test/reset buttons	15A 120V/1800W UL Listed	25A	2	6	.36
02821	6	12/3 SJTW GFCI w handle, test/reset buttons	20A 120V/1800W UL Listed	25A	2	6	.36

User Attachable

Convert your extension cords, tools, and equipment to add GFCI protection.



02831

PAT NO	LENGTH IN FT	DESCRIPTION	AMP/VOLT/WATT/RATING	RELAY CAPACITY	MASTER PACK	MASTER WT	MASTER PK CUBE
02831	-	15A User-Attachable GFCI	15A 120V/1800W UL/CSA Listed	15A	10	7	1.0

Plug-In with Surge Protection

Converts any standard receptacle into a GFCI surge protected outlet.



02800

PAT NO	LENGTH IN FT	DESCRIPTION	AMP/VOLT/WATT/RATING	RELAY CAPACITY	MASTER PACK	MASTER WT	MASTER PK CUBE
02800	-	15A GFCI Converter for Standard Receptacles	15A 120V/1800W UL Listed	15A	12	8	.34

