



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



09733 3' Appliance Cord *Southwire Company*

| | |
|------------------|----------------------------|
| Catalog Number | 09733 |
| Manufacturer | Southwire Company |
| Description | 16/3 3' SPT-3 PWR Sply S/P |
| Weight per unit | 0.2400 (lbs/ft) |
| Product Category | Portable Cord Sets |

Features

| | |
|----------------------|--------------|
| amperage rating | 13 |
| Conductor Size | 16 |
| connection | 5-15P |
| core | PVC |
| media | Yes |
| Number of Conductors | 2 |
| outside diameter | 0.089 |
| Resistance | -20 to +60 C |
| strands | 26/30 |
| Voltage Rating | 5 +/-1 mA |

Material, Color, and Finish

| | |
|---------------------|--------|
| Color | PVC |
| Conductor Material | Copper |
| Insulation Material | PVC |
| Jacket Material | PVC |

Dimensions and Weight

| | |
|--------|---|
| Length | 3 |
|--------|---|

Descriptions

| | |
|------------------------|--------------------------------------|
| extra long description | SWC 9733SW8809 CORD, POWER SUPPLY 1 |
| Long Description | 16/3 3' SPT-3 PWR SPLY S/P |
| Product Type | Cord, Power Supply 16/3 3' SPT-3 S/P |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cables & Cords |
| GTIN | 00029892097332 |
| Manufacturers Part Number | 9733SW8809 |
| UPC | 029892097332 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | CORD SETS [DRYER & RANGE CORDS & BOOSTER CABLES] |
| Type | Cord Set |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 25 |
| Weight | 0.238 |
| Weight Per foot | 0.24 |

Uses, Certifications, and Standards

| | |
|--------------------|----------------|
| Application | Extension Cord |
| standard | UL817 |
| Temperature Rating | -40 to + 60 C |