



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1550 Wilson Rd.
77338-0000, TX Humble
Phone: 281-548-0169
Fax: 281-548-0198



OS60FB5 60" FB Outdoor Super Pro Wet Rated Fan

Craftmade International I

Catalog Number	OS60FB5
Manufacturer	Craftmade International I
Description	The Ideal Combination Of Excellent Performance, Exceptional Value and Timeless Style, The Wet Rated Craftmade Outdoor Super Pro 60" Ceiling Fan Featuring A Clean Motor, Updated Canopy and Straight Blade Arms Is Built For Performance. The Dual Mount, Heavy-Duty, 3-Speed, Reversible Fan With Custom 60" Abs Blades Is Built to Deliver Performance With Style.
Weight per unit	22.8 (lbs/each)
Product Category	20241126102637

Features

Category	Fans
Safety Rating	Wet
Voltage	120.00

Material, Color, and Finish

Finish	Black
Style	Transitional

Descriptions

Description	60" FB OUTDOOR SUPER PRO WET RATED FAN
Long Description	The ideal combination of excellent performance, exceptional value and timeless style, the wet rated Craftmade Outdoor Super Pro 60" ceiling fan featuring a clean motor, updated canopy and straight blade arms is built for performance. The dual mount, heavy-duty, 3-speed, reversible fan with custom 60" ABS blades is built to deliver performance with style.
Product Type	60"Ceiling Fan

Manufacturer Information

Brand	CRAFTMADE
GTIN	00647881235659
Manufacturers Part Number	OS60FB5
UPC	647881235659

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Wet Location

Packaging

Carton	1
Weight Per each	22.77