



Open Switches
T&B Catalog Number:

OT25FT3
 80432541546
 Active

UPC Number:
Status:
Description:

3 pole, 25 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

Application

- Industrial control panel disconnects
- For use in motor controller and motor overload protection applications
- Can be used as an OSHA lockout/tagout disconnect

General

| | |
|-----------------|--------------|
| Style | Door Mounted |
| Number of Poles | 3 |
| Series | Non-fusible |

Approvals

| | |
|----------|--------|
| UL Class | UL 508 |
|----------|--------|

Dimension Information

| | |
|--------------------|--------------------|
| H x W x D (inches) | 2.13 x 1.69 x 2.64 |
|--------------------|--------------------|

Specifications

| | |
|----------------------|-----|
| Rated Current (Amps) | 25 |
| Rated Voltage AC | 600 |

Packaging

| | |
|--------------------|----------------|
| T&B Inner Pack | 1 |
| Package in Units | 10 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.23 lbs. Each |

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com



Open Switches
T&B Catalog Number:

OT25FT3
 80432541546
 Active

UPC Number:
Status:
Description:

3 pole, 25 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

Application

- Industrial control panel disconnects
- For use in motor controller and motor overload protection applications
- Can be used as an OSHA lockout/tagout disconnect

General

| | |
|-----------------|--------------|
| Style | Door Mounted |
| Number of Poles | 3 |
| Series | Non-fusible |

Approvals

| | |
|----------|--------|
| UL Class | UL 508 |
|----------|--------|

Dimension Information

| | |
|--------------------|--------------------|
| H x W x D (inches) | 2.13 x 1.69 x 2.64 |
|--------------------|--------------------|

Specifications

| | |
|----------------------|-----|
| Rated Current (Amps) | 25 |
| Rated Voltage AC | 600 |

Packaging

| | |
|--------------------|----------------|
| T&B Inner Pack | 1 |
| Package in Units | 10 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.23 lbs. Each |

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com