



**H221 - SHALLOW IC HOUSING**

| Source  | Model  | Description  |
|---------|--|--|
| H221    | IC Housing with hanger bars, junction box and magnetic ballast | Integral 120V 60 Hz magnetic fluorescent ballast for one 13W Twin Tube 2-pin Compact Fluorescent lamp (F13TT, GX23 base). Junction box listed for through branch circuit wiring and has two 3/4" and five 1/2" knockouts. Bar hangers will span 24" joists. 3-1/2" height for use in shallow ceilings. May be installed in IC applications. May be installed in ceiling or wall. UL/cUL Damp location listed, Feed through Listed, Replacement Lamp: Available by others or as Halo #Z63 |
| 24P     | Flush Diffuser Trim  |  |
| HOUSING | 8-3/8"L x 4-5/8"D x 3-1/2"H (213mm x 117mm x 89mm)             |  |
| TRIM    | 5-1/2" x 9-1/4" (140mm x 235mm)                                |  |



**H2925T, H2925TW, H2925PL - BRICK LIGHT / AISLE LIGHT**

| Source  | Description  |
|---------|--|
|         | With thermal protector, brown die cast trim, flat unbreakable lens and tamper proof screws. (Non-IC) |
| H2925T  | Incandescent 20W T6 1/2 lamps (Halo Z7). (Damp location listed)                                      |
| H2925TW | Incandescent 20W T6 1/2 lamps (Halo Z7). (Wet location listed)                                       |
| H2925PL | 7W 2-pin, G23 base compact fluorescent lamps or 9W lamp. (UL/cUL Wet location listed)                |
| SD2925  | Tamper proof screwdriver accessory   |
| HOUSING | 7-3/8"L x 3-1/2"D x 2-1/4"H (187mm x 89mm x 57mm)  |
| TRIM    | 8-7/8"L x 3-1/2"H (225mm x 89mm)   |



**H2926TW - BRICK LIGHT / AISLE LIGHT**

| Source    | Description   |
|-----------|---|
|           | With thermal protector, brown die cast trim, glare reducing shade and tamper proof screws. (Non-IC) |
| H2926TW   | Incandescent 20W T6 1/2 lamps (Halo Z7). (Wet location listed)                                      |
| ACCESSORY | Tamper proof screwdriver accessory  |
| HOUSING   | 7-3/8"L x 3-1/2"D x 2-1/4"H (187mm x 89mm x 57mm)   |
| TRIM      | 8-7/8"L x 3-1/2"H (225mm x 89mm)  |



**H2920ICT - STEP LIGHT**

| Source   | Description   |
|----------|---|
| H2920ICT | Step Light with white louver trim. Wiring connections are made in fixture. 25W A19 lamp. (IP Rated) |
| HOUSING  | 8"L x 3-1/2"D x 4-1/2"H (203mm x 89mm x 114mm)  |
| TRIM     | 9-3/8"L x 5-3/4"H (238mm x 146mm)   |
| FINISH   | White (P)   |



**H2922ICT - STEP LIGHT**

| Source   | Description  |
|----------|--|
| H2922ICT | Step Light with white louver trim. Fixture is prewired to junction box. UL/cUL listed junction box rated for feed through. 25W A19 lamp. IC rated for direct contact with insulation and combustible materials. (IP Rated) |
| HOUSING  | 11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm)  |
| TRIM     | 9-3/8"L x 5-3/4"H (238mm x 146mm)  |
| FINISH   | White (P)  |



**H2922-120PL - STEP LIGHT**

| Source      | Description  |
|-------------|--|
| H2922-120PL | Step Light with white louver trim. Fixture is prewired to junction box. UL/cUL listed junction box rated for feed through. Integral 120V, 60 Hz magnetic ballast. (5W / 7W / 9W Twin Tube 2-pin CFL) |
| HOUSING     | 11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm)  |
| TRIM        | 9-3/8"L x 5-3/4"H (238mm x 146mm)  |
| FINISH      | White (P)  |

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit [www.cooperlighting.com](http://www.cooperlighting.com) for available options, accessories and ordering information.



**H2900T - THRU-WALL LIGHT, NON-IC**

| Source  | Description   |
|---------|---|
| H2900T  | Provides lighting on each side of wall. 100W A19. (Albalite Glass Lens) |
| HOUSING | 13-1/2"L x 4"D x 8-1/4"H (343mm x 102mm x 210mm)                        |
| TRIM    | 11-3/8"L x 7-3/4"H (289mm x 197mm)                                      |
| FINISH  | White (P)   |



**H2932ICTW - LENSED WALL / STEP LIGHT**

| Source    | Description   |
|-----------|---|
| H2932ICTW | UL/cUL Listed for wall mounting in insulation. IC rated for direct contact with insulation and combustible material, UL/cUL listed for damp location; and feed through. (White trim with Albalite Glass Lens) |
| HOUSING   | 11-1/2"L (enclosure and J-Box) x 5-1/2"D x 3-1/2"H (292mm x 140mm x 89mm)   |
| TRIM      | 5-3/4"L x 9-3/8"H (146mm x 238mm)   |
| LAMP      | 25W, A19 max.   |
| FINISH    | White (P)   |



**H2932T - CLOSET LIGHT / SHALLOW RECTANGLE, NON-IC**

| Source  | Description   |
|---------|---|
| H2932T  | White trim with albalite diffuser. Junction box rated for feed through branch applications. (For Non-Insulated Ceilings. UL/cUL Listed) |
| HOUSING | 11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm)   |
| TRIM    | 9-3/8"L x 5-3/4"H (238mm x 146mm)   |
| LAMP    | 60W, A19 max.   |
| FINISH  | White (P)   |



**H37T-401AL - HEAT LIGHT, NON-IC**

| Source     | Description  |
|------------|--|
| H37T-401AL | For Non-Insulated Ceilings. IP Rated (Improper Lamp) |
| HOUSING    | 8"OD x 5-1/2"H (203mm x 140mm)                       |
| TRIM RING  | Brushed Aluminum                                     |
| LAMP       | 250W Infra-Red                                       |



**477 - POWER-TRAC ADAPTER TRIM**

| Source | Description  |
|--------|--|
| 477    | Allows (120V) Trac Lampholders (150W max) to be used with recessed installations. (Use with H7T, H7ICT, H27T, H7RT, H7RICT, H27RT and H44T housings) |
| OD     | 7-1/4" (184mm)   |
| FINISH | White with Black Baffle (477P), White with White Baffle (477W)   |



**DICHROIC COLOR FILTERS**

| Source | Model                  |
|--------|------------------------|
| L114   | UV Filter              |
| L120   | Red                    |
| L121   | Amber                  |
| L122   | Yellow                 |
| L123   | Green                  |
| L124   | Daylight               |
| L125   | Blue                   |
| L127   | Cosmetic Color Filters |
| L130   | Yellow                 |

For low voltage MR16 units.



**OPTICAL LENSES**

| Source | Model                     |
|--------|---------------------------|
| L110   | Diffuse Sand Blasted Lens |
| L111   | Soft Focus Textured Lens  |
| L113   | Prismatic Lens            |
| L115   | Linear Spread Lens        |


For Low Voltage MR16 units

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit [www.cooperlighting.com](http://www.cooperlighting.com) for available options, accessories and ordering information.



**DESIGNER FINISH TRIM RINGS**

| Source  | Model         | Description  |
|---------|---------------|--|
| TRM6P   | White Metal   | Metal 7 1/4" OD (184mm). (Compatible with 310°, 312°, 376, 378, 400, 404, 405, 406SC, 406RG, 409, 410, 416, 419, 420, 424, 425, 426°, 429°, 446, 448, 455CG, 455SC, 456P, 456W, 477, 478, 1412, 1416, 1475, 2412, 2416, 2475)<br><br>*Supplied with TRM6P white metal trim rings (All others are supplied with white plastic trim rings) |
| TRM6C   | Chrome        |  |
| TRM6SN  | Satin Nickel  |  |
| TRM6TBZ | Tuscan Bronze |  |
| TRM6MB  | Black Metal   |  |
| TRM7MB  | Black Plastic |  |



**OVERSIZED TRIM RINGS**

| Source  | Size                                   | Description   |
|---------|--|---|
| OT400P  | 6" ID X 9-1/4" OD (152mm x 235mm)      | Oversized white metal trim ring. (May be used behind any Halo H7/H750 trim family)  |
| OT403P  | 6" ID X 8" OD (152mm x 203mm)          | Oversized white plastic trim ring. (Compatible with 310, 312, 376, 378, 400, 404, 405, 406 (SC and RG only), 409, 410, 416, 419, 420, 424, 425, 426, 429, 446, 448, 477, 478, 1412, 1416, 1475, 2412, 2416, 2475) |
| OT999P  | 4" ID x 5-3/4" OD (102mm x 146mm)      | Oversized white metal trim ring. (Compatible with 990, 992, 993, 994, 996, 998, 999, 1419, 1420, 1421, 1493 and 1498)   |
| OT460P  | 7-1/2" ID x 11-1/4" OD (191mm x 286mm) | Oversized white metal trim ring compatible with 466, 468 and 480 trims  |
| OT490WH | 5-3/16" ID x 9-1/4" OD (132mm x 235mm) | White aluminum ring use with ML7x LED modules: 600 Series, 900 Series and 1200 Series   |
| 800PGR  | 7-1/2" ID x 8-5/8" OD (191mm x 219mm)  | H800 oversized trim ring  |
| OT500P  | 6" ID x 7 1/4" OD (152mm x 184mm)      | Oversized white polymer trim ring for use with H5 series straight sided trims   |



**DESIGNER TRIM RINGS**

| Source | Size                                   | Finishes   | Description  |
|--------|--|--|--|
| TRM400 | 3-3/8" ID X 5-1/8" OD (86mm x 130mm)   | PC - Polished Chrome<br>BK - Black<br>WH - White<br>SN - Satin Nickel<br>TBZ - Tuscan Bronze | For H4 LED TL4 Series LED Trims. Die cast trim ring replaces standard ring included with each trim. (Thin profile provides subtle ceiling appearance)<br>0.12" OD x 0.18" ID (4mm x 5mm) |
| TRM490 | 5-3/16" ID x 7-1/4" OD (132mm x 184mm) |  | For H7 LED 49x Series LED Trims. Die cast trim ring replaces standard ring included with each trim. (Thin profile provides subtle ceiling appearance)<br>0.12" OD x 0.18" ID (4mm x 5mm) |



**TRANSFORMERS**

| Source  | Description   |
|---------|---|
| H277    | Steps 277V line voltage down to 120V fixture operating voltage. 300VA max. (For use with Non-IC housings) |
| H347    | Same as above but steps 347V down to 120V, 75 VA max. (For use with Non-IC housings)                      |
| H347200 | Same as above but steps 347V down to 120V, 200 VA max. (For use with Non-IC housings)                     |



**HANGING BARS**

| Source | Description  |
|--------|--|
| HB224  | One piece hanger bar for 24" maximum joist spacing. (Set of two)   |
| HB424  | Two piece hanger bar for 24" maximum joist spacing. (Set of four pieces, order one HB424 per fixture)    |
|        | Hanger bars are compatible with the following housing families: M700, H800, H801, H802, H803, and H880E. |



**SLOPE ADAPTERS**

| Description  |  | Slope      | 0°     | 5°    | 10°           | 15°    | 20°           | 25°    | 30°           | 35°    | 40°    | 45°    |
|--|--|------------|--------|-------|---------------|--------|---------------|--------|---------------|--------|--------|--------|
| White .050 spun aluminum. Available as shown in following table. Items in <b>BOLD</b> face are stocked |  | 6" for H44 | HSA680 | HSA65 | <b>HSA610</b> | HSA615 | <b>HSA620</b> | HSA625 | <b>HSA630</b> | HSA635 | HSA640 |        |
|  |  | 8" for H46 |        | HSA85 | <b>HSA810</b> | HSA815 | <b>HSA820</b> | HSA825 | <b>HSA830</b> | HSA835 | HSA840 | HSA845 |

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit [www.cooperlighting.com](http://www.cooperlighting.com) for available options, accessories and ordering information.



**AIR-TITE™ Gaskets**

**Description**

**GA-ATH5-6PK**  
H5ICAT Air-Tite™ 6-pack gaskets for installation at finished ceiling opening

**GA-ATH7-6PK**  
H7ICAT Air-Tite™ 6-pack gaskets for installation at finished ceiling opening



**TRIM GASKETS**

**Description**

**GA-ATTRIM-6PK**  
Accessory / spare trim gasket for use with H7 and EI/ET 700 family trims.



**SOCKET EXTENDER**

**Description**

**H1999**  
For use with selected trims and housings. Extends lamp 1" (25mm)



**MOUNTING CLIPS**

**Description**

**TB7**  
T-Bar attachment clips. Set of four. Order one set per fixture. Can also be used with HB424 and HB224 Hanger Bars

**RK7**  
Hold down clips for non-remodel fixtures when hanger bars are not used. (Set of four)



**R LAMP ACCESSORY**

**Description**

**H930**  
R/PAR lamp aiming accessory for H7T, H7TNB, H7RT, H7ICT, H7ICAT, H7RICT, H7RICAT, H7ICTNB, H7ICATNB housings with 310 and 426 trims. Allows lamp to be aimed up to 30° from vertical and rotated 358°. See housing-trim selection for lamp listings



**SCREWDRIVER**

**Description**

**SD2925**  
Screwdriver for tamper resistant screws supplied with H2925 and H2926 brick lights



**4 COIL SPRINGS**

**Description**

**RS7H**  
Set of 4 coil springs for use with 301, 310, 401 and 426 trims in the H7 recessed housing family



**LAMPS**

**Description**

**COMPACT FLUORESCENT**

Z62 22W 15mm PL-C, Gx32d-2 Double Twin Tube Compact Fluorescent (2700°K)

Z128 28W 15mm PL-C Gx32d-3 Double Twin Tube (DTT) 2-Pin Compact Fluorescent (2700°K)

Z63 13W Twin Tube Compact Fluorescent, 2-pin, Gx23 (2700°K)

Z64 13W Double Twin Tube Compact Fluorescent, 2-pin, Gx23-2 (2700°K)

Z113E 13W Double Twin Tube (DTT) 4-Pin Compact Fluorescent, G24q-1 (2700°K)

Z118 18W Double Twin Tube (DTT) 2-Pin Compact Fluorescent, G24d-2 (2700°K)

Z118E 18W Double Twin Tube (DTT) 4-Pin Compact Fluorescent G24q-2 (2700°K)

Z126E 26W Double Twin Tube (DTT) 4-Pin Compact Fluorescent, G24q-3 (2700°K)

Z126P30 26W Triple Twin Tube (TTT) 4-Pin PL Compact Fluorescent, GX24q-3 (3000°K)

Z132P30 32W Triple Twin Tube (TTT) 4-Pin PL Compact Fluorescent, GX24q-3 (3000°K)

Z142P30 42W Triple Twin Tube (TTT) 4-Pin PL Compact Fluorescent, GX24q-4 (3000°K)

Z118TE30 18W Triple Twin Tube (TTT) 4-Pin Compact Fluorescent, GX24q-2 (3000°K)

Z126TE30 26W Triple Twin Tube (TTT) 4-Pin Compact Fluorescent, GX24q-3 (3000°K)



**LAMPS**

**Description**

**LOW VOLTAGE**

Z21 12V Q50W MR16 NSP

Z26 12V Q50W MR16 NFL

Z31 12V Q50W MR16 FL

Z40 12V Q75W MR16 NSP

Z45 12V Q75W MR16 FL

Z121 50W MR16/Q/10°/TL (GE TURN-AND-LOCK BASE)

Z131 50W MR16/Q/20°/TL (GE TURN-AND-LOCK BASE)

Z124 50W MR16/Q/40°/TL (GE TURN-AND-LOCK BASE)



**LAMPS**

**Description**

**INCANDESCENT**

Z7 20W T 6 1/2" IF

Z9 40W R16 FL

Z10 100W BR25

Z28 120V GU10 base, line voltage MR16

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit [www.cooperlighting.com](http://www.cooperlighting.com) for available options, accessories and ordering information.