

# Eaton 10250H5300

Catalog Number: 10250H5300

Eaton 10250T pushbutton, 10250H, Assembled control station, 30.5 mm, Heavy-Duty, NEMA 1, Black, Flush, Die cast, FOR/REV/STOP, Surface, Three element



## General specifications

### Product Name

Eaton 10250T pushbutton

### Catalog Number

10250H5300

### UPC

782113203119

### Product Length/Depth

7.7 in

### Product Height

4.2 in

### Product Width

4.6 in

### Product Weight

1.35 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CE Marked

### Certifications

UL 505

CSA Certified

### Catalog Notes

Black Bezel

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Heavy-Duty

### Actuator color

Black

### Enclosure

NEMA 1

### Actuator

Flush

### Enclosure material

Die cast

### Legend

FOR REV STOP

### Illumination

Standard

### Series

10250H

### Product category

Assembled control station

### Number of elements

3

### Mounting method

Surface

### Degree of protection

NEMA 3R

NEMA 12

NEMA 3

NEMA 13

NEMA 3S

NEMA 4

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250H5300



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)