



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250TB64 Button B *Eaton Corp*

Catalog Number	10250TB64
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton Operator Button, 10250T Series, Non-Illuminated Push-Pull Operator Button, Blue Actuator, Legend: Blank Legend, Standard (40 MM)
Weight per unit	1.0 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

dimensions	1.6000 IN X 1.6000 IN X 0.5000 IN
media	Yes

Dimensions and Weight

Size	Standard 40 mm
------	----------------

Descriptions

Description	BUTTON B
extra long description	ETN 10250TB64 BUTTON B
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton operator button, 10250T series, Non-illuminated Push-Pull Operator Button, Blue actuator, Legend: Blank legend, Standard (40 mm)
Product Type	Button B

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113651675
Manufacturers Part Number	10250TB64
UPC	782113651675

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	Pushbutton accessory

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Datacenters - Facilities: Power Distribution
Commercial / Institutional Buildings / Structures - Critical Power
Utility/Industrial Facilities & Factories - Facility: Critical Power
Stationary Machinery and Equipment Outside Factory - Stationary
Machinery and Equipment Outside Factory - Other

standard

UL Listed, CSA Certified, CE Marked