



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



11100RQD03 Ac/DC Right Angle Thru Beam Source Wide Angle With *Eaton Corp*

Catalog Number	11100RQD03
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Through Beam, Right Angle, Power, Dual Key Micro, 4 Pin, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	0.7000 (lbs/each)
Product Category	Sensor Accessories

Features

connection	Dual key micro
dimensions	2.5500 IN X 0.4700 IN X 0.7100 IN

Descriptions

Description	AC/DC RIGHT ANGLE THRU BEAM SOURCE WIDE ANGLE WITH
extra long description	ETN 11100RQD03 18MM TB SOURCE RA,20
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Through Beam, Right Angle, Power, Dual key micro, 4 pin, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	18MM TB Source Ra, 20-264VACDC, Micro Conn

Manufacturer Information

Brand	Eaton
GTIN	00782113843377
Manufacturers Part Number	11100RQD03
UPC	782113843377

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous commercial & industrial devices
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.7

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature standard	-4° to 158°F (-20° to 70°C) cUL Recognized, UL Recognized