

Canopy Switch

1200



Pressure Sensitive Door & Canopy Switch,
15 Amp 120 Vac, 15 Amp 250 Vac



features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

specifications

General Info

Type: Pressure Sensitive Door & Canopy Switches
Number Of Poles: 1
Style: Decorator

Listing Agencies/Third Party Information

UN SPS C: 39121507

Dimensions

Depth U S: 1.547"
Height U S: 3.188"
Width U S: 1.516"

Technical Information

Amps: 15 Amp
Volts: 120/250VAC
Volts A C: 120

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant