



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 12100R6513 Comet Thru-Beam Detector Wide Angle Right Angle Ac *Eaton Corp*

Catalog Number	12100R6513
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Through Beam, 20 FT Range, Right Angle, Output On, 6.6 FT, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, PVC, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	0.5000 (lbs/each)
Product Category	Sensor Accessories

### Features

dimensions	2.5500 IN X 0.4700 IN X 0.7100 IN
------------	-----------------------------------

### Dimensions and Weight

Height	0.71
Length	2.55
Width	0.47

### Descriptions

Description	COMET THRU-BEAM DETECTOR WIDE ANGLE RIGHT ANGLE AC
extra long description	ETN 12100R6513 18MM TB DETECTOR,WID
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Through Beam, 20 ft range, Right Angle, Output ON, 6.6 ft, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, PVC, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	18MM TB Detector, Wide Ang, RT Ang, Ac/

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113821962
Manufacturers Part Number	12100R6513
UPC	782113821962

### Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

### Packaging

Carton	1
Weight Per each	0.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Vehicles: On-Road - PickUp & Delivery: Food .....
Operating Temperature .....	-4° to 158°F (-20° to 70°C) .....
standard .....	cUL Recognized,UL Recognized .....