



Atlanta, Georgia

Phone 800-521-7326

Fax 770-745-1333

Hex Washer Head Self Drill Screw Type 4/Type 5



Peco Catalog#	UPC	Size	Point Type	Max Drill Thickness	Finish	Package Type
1224X78HTJ	705591 03110 4	12-24 X 7/8	#4 Milled	.250	Stalgard	Jar
i1224X114HT	705591 03385 6	12-24 X 1-1/4	#5 Forged	.500	Zinc	Box
l1224X114HJTJ	705591 03386 3	12-24 X 1-1/4	#5 Forged	.500	Zinc	Jar
1224X114HT	705591 03378 8	12-24 X 1-1/4	#5 Milled	.500	Stalgard	Box
1224X114HTJ	705591 03377 1	12-24 X 1-1/4	#5 Milled	.500	Stalgard	Jar
1224X112HTJ	705591 00295 1	12-24 x 1-1/2	#5 Milled	.500	Stalgard	Jar
1224X2HT	705591 03379 5	12-24 x 2	#5 Milled	.500	Stalgard	Box
1224X2HTJ	705591 03113 5	12-24 X 2	#5 Milled	.500	Stalgard	Jar

Stalgard Coating provides 1000 hours of salt spray resistance per ASTM B117 & is RoHS Compliant

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.