



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5575 Ruben M Torres Blvd
78526-0000, TX Brownsville
Phone: 956-295-3007
Fax: 956-295-3008



1250I Switch Moment Control 15A 120/277V (SPDT) Iv

Pass & Seymour/Legrand

Catalog Number	1250I
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Double-Throw Switch. 15A, 120/277VAC Rating. Tested to 3 Amps, 24VDC Rating.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

action	SP, DT
actuator	Toggle
amperage rating	15
Contact Rating	15Amp, 120/277V
insulation	Bare
Material	Nylon
Mounting Type	Box
Poles	1
Switch Type	Momentary
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Ivory
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	SWITCH MOMENT CONTROL 15A 120/277V (SPDT) IV
extra long description	P&S 1250I SW MOMENT CONTRL 15A 120
Features	Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.
Long Description	Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.
Product Type	SW Moment Contrl 15A 120/277V (SPDT) I
Special Features	Side wire terminals, Fiber Terminal insulation barrier\



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5575 Ruben M Torres Blvd
78526-0000, TX Brownsville
Phone: 956-295-3007
Fax: 956-295-3008

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007125016
Manufacturers Part Number	1250-I
UPC	785007125016

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL CSA, UL, CULUS, UL listed