



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1250L SW Moment Control 15A 120/277V Lock Gy

Pass & Seymour/Legrand

Catalog Number	1250L
Manufacturer	Pass & Seymour/Legrand
Description	Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC Rating, Tested to 3A, 24VDC Rating.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

amperage rating	15
Contact Configuration	NO
Contact Rating	15amp, 120/277vac
insulation	Bare
Poles	spdt
Voltage	120.0 V
Voltage Rating	120/277
Wattage	1
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Locking
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	SW MOMENT CONTROL 15A 120/277V LOCK GY
extra long description	P&S 1250L SW MOMENT CNTRL 15A 120/
Long Description	Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating, Tested to 3A, 24VDC rating.
Product Type	SW Moment CNTRL 15A 120/277V Lock Gy
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007125023
Manufacturers Part Number	1250-L
UPC	785007125023

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Manual Controller Switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 15.0

Packaging

Carton 1

Package 10

Weight Per each 0.275

Uses, Certifications, and Standards

Application Industrial

Enclosure Box or NEMA 1 sheet steel

Mounting WALL

standard UL Listed