

# Manual Controller

1251L



Single Pole, Double Throw Manual Control Switch, 20 amps, 120/277 volts, Locking.



## features & benefits

- Oversize silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers, and toggles molded of durable nylon.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Locking Switches supplied with one 1498-NT key.
- Normally open.

## specifications

### General Info

Type: Momentary Contact

Number Of Poles: 1

Special Features: Three Position

### Listing Agencies/Third Party Information

CSA Listing Info: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes  
UN SPS C: 39121507  
UR: No

**Dimensions**

Depth U S: 1.469"  
Height U S: 3.281"  
Weight: 0.25928  
Width U S: 1.5"

**Technical Information**

Amps: 20 Amp  
Volts: 120/277VAC  
Volts A C: 120/277

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant