



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1251RED SW CTR Off Control 20A 120/277V (SPDT) RD

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 1251RED |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V. |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Fan Speed Switches & Controls |

Features

| | |
|------------------|---------------|
| actuator | Toggle |
| amperage rating | 20 |
| connection | Side wire |
| load | 20A |
| operating cycles | 50000 |
| Poles | 1 |
| Voltage Rating | 120/277 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|---|
| Size | 1.469" Depth x 1.5" Width x 3.281" Height |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | SW CTR OFF CONTROL 20A 120/277V (SPDT) RD |
| extra long description | P&S 1251RED SW CTR OFF CONTRL 20A 1 |
| Long Description | Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V. |
| Product Type | SW CTR Off Contrl 20A 120/277V (SPDT) RD |
| Special Features | Single Pole, Double Throw Manual Control Switch |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007026283 |
| Manufacturers Part Number | 1251-RED |
| UPC | 785007026283 |

Taxonomies, Classifications, and Categories

| | |
|------|-------------------|
| Type | Manual Controller |
|------|-------------------|

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.275 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial/Industrial |
| environmental conditions | UL94 V2 |
| Frequency Rating | 60Hz |
| Mounting | BOX |
| Operating Temperature | Maximum continuos +75°C, minimum -40°C |
| standard | CULUS, CSA, UL, RoHS, UL Listed, CSA Listed |