

---

## MANUAL CONTROLLER

1251W | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Single Pole, Double Throw Manual Control Switch, 20 amps, 120/277 volts, White.



Oversize silver alloy contacts for long life and better heat dissipation. Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. Fiber terminal insulation barriers standard. Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. Bodies, covers, and toggles molded of durable nylon. Single Pole-Double Throw and Double Pole-Double Throw. Locking Switches supplied with one 1498-NT key. Normally open.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Type: Momentary Contact  
Number Of Poles: 1  
Special Features: Three Position

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
UL Listing No: Yes  
UN SPSC: 39121507

#### DIMENSIONS

Depth (US): 1.469"  
Height (US): 3.281"  
Width (US): 1.5"  
Weight: 0.0288

**TECHNICAL INFORMATION**

Amps: 20A

Volts: 120/277VAC

Volts (AC): 120/277

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



---

## MANUAL CONTROLLER

1251W | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Single Pole, Double Throw Manual Control Switch, 20 amps, 120/277 volts, White.



Oversize silver alloy contacts for long life and better heat dissipation. Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. Fiber terminal insulation barriers standard. Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. Bodies, covers, and toggles molded of durable nylon. Single Pole-Double Throw and Double Pole-Double Throw. Locking Switches supplied with one 1498-NT key. Normally open.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Momentary Contact

Number Of Poles: 1

Special Features: Three Position

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes

UL Listing No: Yes

UN SPSC: 39121507

#### DIMENSIONS

Depth (US): 1.469"

Height (US): 3.281"

Width (US): 1.5"

Weight: 0.0288

## TECHNICAL INFORMATION

Amps: 20A

Volts: 120/277VAC

Volts (AC): 120/277

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

