

# Eaton 1257-SP

Catalog Number: 1257-SP

Eaton power device receptacle, Dryer, #12 - 4 AWG, 30A, Flush, 125/250V, Back, Black, NEMA 14-30R, Three-pole, Four-wire, Three-pole, four-wire, grounding, Screw, Glass-filled nylon, Power, Used with S21



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton power device receptacle	1257-SP
<b>UPC</b>	<b>Product Length/Depth</b>
032664306808	2.5 in
<b>Product Height</b>	<b>Product Width</b>
8.5 in	5 in
<b>Product Weight</b>	<b>Compliances</b>
0.3 lb	RoHS Compliant
	NAFTA
<b>Certifications</b>	
UL Listed	
CSA Certified	
NOM	

## defaultTaxonomyAttributeLabel

### Used with

S21

### Special features

Dryer

### Amperage Rating

30A

### Voltage rating

125/250 V

### Wiring method

Back

### Number of wires

4

### Mounting method

Flush

### Number Of Poles

Three-pole

### Color

Black

### Connection type

Screw

### Style

Power

### Allowable wire size

#12-4 AWG

### NEMA configuration

14-30R

### Torque rating

25 lbf-inch

### Design type

Receptacle

### Material

Glass filled nylon

### Receptacle type

Three-pole, four-wire, grounding

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1257-SP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton 1257-SP

Catalog Number: 1257-SP

Eaton power device receptacle, Dryer, #12 - 4 AWG, 30A, Flush, 125/250V, Back, Black, NEMA 14-30R, Three-pole, Four-wire, Three-pole, four-wire, grounding, Screw, Glass-filled nylon, Power, Used with S21



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton power device receptacle	1257-SP
<b>UPC</b>	<b>Product Length/Depth</b>
032664306808	2.5 in
<b>Product Height</b>	<b>Product Width</b>
8.5 in	5 in
<b>Product Weight</b>	<b>Compliances</b>
0.3 lb	RoHS Compliant
	NAFTA
<b>Certifications</b>	
UL Listed	
CSA Certified	
NOM	

## defaultTaxonomyAttributeLabel

### Used with

S21

### Special features

Dryer

### Amperage Rating

30A

### Voltage rating

125/250 V

### Wiring method

Back

### Number of wires

4

### Mounting method

Flush

### Number Of Poles

Three-pole

### Color

Black

### Connection type

Screw

### Style

Power

### Allowable wire size

#12-4 AWG

### NEMA configuration

14-30R

### Torque rating

25 lbf-inch

### Design type

Receptacle

### Material

Glass filled nylon

### Receptacle type

Three-pole, four-wire, grounding

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1257-SP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)