



Powering Business Worldwide

**125**

Recp Single Surface 30A 125/250V 3P3W BK

UPC: 032664196508

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 20 Amp  
Voltage Rating: 250 Vac  
Material: Nylon  
Color: Ivory  
NEMA Rating: 6-20R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height X 1.30 In Length  
Environmental Conditions: See Spec Sheet  
Dielectric Strength: 2000 V  
Insulation: Nylon  
Temperature Rating: -20C to 70C (-4F to 158F)

**1251**

bRecp Single Surface 50A 125V 2P3W BK

UPC: 032664306402

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Single, Straight Blade  
Special Features: Wiring Type Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 250 Vac  
Material: Nylon  
Color: Brown  
NEMA Rating: 6-15R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height X 1.30 In Length  
Environmental Conditions: See Spec Sheet  
Dielectric Strength: 2000 V  
Insulation: Nylon  
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

## 1252

Recp Single Surface 50A 250V 2P3W BK<sub>n</sub>

UPC: 032664306501

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Single, Straight Blade  
Special Features: Wiring Type Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 250 Vac  
Material: Nylon  
Color: Ivory  
NEMA Rating: 6-15R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height X 1.30 In Length  
Environmental Conditions: See Spec Sheet  
Dielectric Strength: 2000 V  
Insulation: Nylon  
Temperature Rating: -20C to 70C (-4F to 158F)

## 1253-BOX

Recp Single Flush 50A 125V 2P3W BK

UPC: 032664306600

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Single, Straight Blade  
Special Features: Wiring Type Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Nylon  
Color: Brown  
NEMA Rating: 5-15R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height X 1.30 In Length  
Environmental Conditions: See Spec Sheet  
Dielectric Strength: 2000 V  
Insulation: Nylon  
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

### 1254-BOX

Recp Single Flush 50A 250V 2P3W BK

UPC: 032664306709

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Single, Straight Blade  
Special Features: Wiring Type Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Nylon  
Color: Ivory  
NEMA Rating: 5-15R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height X 1.30 In Length  
Environmental Conditions: See Spec Sheet  
Dielectric Strength: 2000 V  
Insulation: Nylon  
Temperature Rating: -20C to 70C (-4F to 158F)

### 1254-BU;1

1254 Recp W/O Zinc Plated Strap BR

UPC: 032664591679

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Single, Straight Blade  
Special Features: Wiring Type Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Nylon  
Color: White  
NEMA Rating: 5-15R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height X 1.30 In Length  
Environmental Conditions: See Spec Sheet  
Dielectric Strength: 2000 V  
Insulation: Nylon  
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

**1257-SP**

Recp Single Flush 30A 125/250V 3P4W BK

UPC: 032664306808

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features: Premium Hospital Grade, Wiring Type Back and Side Wire

Application: Commercial grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, Glass Filled Nylon Base

Color: Brown

NEMA Rating: 6-15R

Mounting: Flush

Connection: Screw

Size: 0.82 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 250 vac

Insulation: Nylon Face, Glass Filled Nylon Base

Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

**1258-BU/20**

1258 Recp W/O Mounting Screws BR

UPC: 032664626876

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features: Premium Hospital Grade, Wiring Type Back and Side Wire

Application: Commercial grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, Glass Filled Nylon Base

Color: Ivory

NEMA Rating: 6-15R

Mounting: Flush

Connection: Screw

Size: 0.82 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 250 vac

Insulation: Nylon Face

Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

**1258-BU;3**

Recp Sgl Flush 50A125/250V ShortStrap BK

UPC: 032664575501

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features: Premium Hospital Grade, Wiring Type Back and Side Wire

Application: Commercial grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, Glass Filled Nylon Base

Color: Brown

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 0.82 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 125 Vac

Insulation: Nylon Face

Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

## 1258-SP

Recp Single Flush 50A 125/250V 3P4W BK

UPC: 032664306907

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features: Premium Hospital Grade, Wiring Type Back and Side Wire

Application: Commercial grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, Glass Filled Nylon Base

Color: Ivory

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 0.82 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 125 Vac

Insulation: Nylon Face

Temperature Rating: -20C to 70C (-4F to 158F)