



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



12NM3106 10/3 6' A/C Whip 1/2" *Southwire Company*

Catalog Number	12NM3106
Manufacturer	Southwire Company
Description	10-3C BK RD GN Non-Metallic Fixture Whips, 1/2"X6' Non-Metallic Liquidtight Conduit - Type LFNC-B , 10 Per Carton, UI Listed
Weight per unit	2.1 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Conductor Size	10
connection	(1) Straight non-metallic liquidtight connector and (1) 90° angle non-metallic connector
gauge	10 AWG
Inside Diameter	0.622/0.642
Material	PVC
Number of Conductors	4
outside diameter	0.82/0.84
Voltage Rating	600V

Material, Color, and Finish

Color	Plain
Conductor Material	Copper
Finish	Gray PVC

Dimensions and Weight

Length	120
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Also Known As...	Liquid Tight Conduit Carflex®
extra long description	AFC 8015 10-3c NMTWH 10PCS/CT
Features	Non-metallic whips are a valuable option for work requiring short cable lengths. Whips are pre-cut lengths of non-metallic conduit, 4 or 6ft long, that are pre-wired, supplied with 12-inch leads for termination, and provided with the appropriate connector on each end, reducing time on the job site. They are great for running power to air conditioning hookups, outdoor lighting, and other outdoor applications such as a disconnect for Jacuzzi or pool filter motors.
Long Description	10-3c BK RD GN Non-metallic Fixture Whips, 1/2"x6' Non-metallic Liquidtight Conduit - Type LFNC-B , 10 per Carton, UL LISTED
Product Type	10-3C NMTWH 10PCS/CT
Short Description	10-3c NMTWH 10PCS/CT
similar brands	Sealtite®

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680137302
Manufacturers Part Number	8015
UPC	077680137302

Taxonomies, Classifications, and Categories

Category Description	NON-METALLIC SEALTITE AND FITTINGS
Type	Type LFNC-B

Trade Size

Trade Size	10-3 STR
------------	----------

Packaging

Carton	1
Package	10
Weight Per each	2.11

Uses, Certifications, and Standards

standard	NEC®410, 430, 440, 250, 356
Temperature Rating	176