



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



130C1X30FT Linerless Rubber Splicing Tape 130C, 1" X 30', BK *Minnesota Mining (3M)*

| | |
|------------------|--|
| Catalog Number | 130C1X30FT |
| Manufacturer | Minnesota Mining (3M) |
| Description | Linerless Rubber Tape, Black, 7.5 LB/In Tensile Strength, 850 % Elongation At Break, +194 °F Operating Temperature, 30 FT Length, 1 In Width, 30 Mil Thickness, 5 Yr Shelf Life, 0.62 LB |
| Weight per unit | 0.0259 (lbs/each) |
| Product Category | Markers & Marking Tapes - Tape |

Descriptions

| | |
|------------------------|---|
| Description | LINERLESS RUBBER SPLICING TAPE 130C, 1" X 30', BK |
| extra long description | 3M 7000006090 Scotch® Linerless Rub |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Scotch |
| GTIN | 00054007417538 |
| Manufacturers Part Number | 130C1X30FT |
| UPC | 054007417538 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------------|
| Category Description | TAPE |
| Type | linerless Ethylene Propylene Rubber |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 24 |
| Weight Per each | 0.0259 |

Uses, Certifications, and Standards

| | |
|----------|--------------------------------------|
| standard | ASTM D-4388 type 1, 2 & 3 HH-I-3825B |
|----------|--------------------------------------|