

Wire Strippers/Cutters

QTR-Turn™ NM Cable Stripper/Cutter KLEIN-KURVE®

Additional Features:

- Exclusive QTR-TURN™* technology to quickly remove outer jacket of NM Cable.
- Strips, cuts, and loops 12 & 14 AWG solid wire.
- Cleanly shears 6-32 and 8-32 screws.
- Serrated nose bends, shapes, and pulls wire.



K1412-3

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM Cable	Screw Shearing	Weight (lbs.)
K1412-3	yellow/blue	7-3/4" (197 mm)	12 & 14 AWG solid (2.5 mm ² & 1.5 mm ²)	12/3 & 14/3	6-32 and 8-32	.41

QTR TURN™ is a trademark of Stride Tool Incorporated *patent pending

Bent Nose NM Romex® Cable Stripper/Cutters KLEIN-KURVE®

Additional Features:

- Patented 90° bent nose for easy work in confined spaces.
- Quickly removes outer jacket of Romex® Cable.
- Strips, cuts, and loops 10, 12 or 14 AWG solid wires.
- Cleanly shears 6-32 & 8-32 screws.
- Serrated nose bends, shapes, and pulls wire.



K90-12/2

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM Cable	Screw Shearing	Weight (lbs.)
K90-10/2	yellow/orange	7-3/8" (187 mm)	10 AWG solid (4.0 mm ²)	10/2	6-32 and 8-32	.41
K90-12/2	yellow/yellow	7-3/8" (187 mm)	12 AWG solid (2.5 mm ²) & 18 AWG stranded (1.0 mm ²)	12/2	6-32 and 8-32	.41
K90-14/2	yellow/white	7-3/8" (187 mm)	14 AWG solid (1.5 mm ²) & 18 AWG stranded (1.0 mm ²)	14/2	6-32 and 8-32	.41

Romex® is a registered trademark of Southwire Company.

Dual NM Cable Stripper/Cutter

- 12/2 and 14/2 stripping slots quickly remove outer jacket of Type NM-B nonmetallic-sheathed cable.
- Cushion grip handles provide comfort.
- Precision-ground stripping holes easily remove insulation on 12 and 14 AWG lead wires.
- Strong-gripping serrated nose; easy bending, shaping and pulling of wire.
- Narrow nose fits into tight places.
- Precision shear-type blades for square, clean cuts on solid copper wire.
- Holes for quick wire looping and bending.
- 6-32 and 8-32 screw-shearing holes.
- Spring-loaded for self-opening action.
- Handy closure lock for convenient storage.



1412

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM-B Cable	Screw Shearing	Weight (lbs.)
1412	yellow	7-7/8" (200 mm)	12 & 14 AWG solid (2.5 mm ² & 1.5 mm ²)	12/2 & 14/2	6-32 & 8-32	.39

Type NM Cable Strippers/Cutters

- Patented stripping slot quickly removes outer jacket of Type NM-B nonmetallic-sheathed cable.
- Handle grips with cushion ridges provide comfort.
- Precision-ground stripping hole easily removes insulation on lead wires.
- Serrated nose easily bends, shapes, or pulls wire.
- Narrow nose fits into tight places.
- Shear-type steel blades for square, clean cuts on solid copper wire.
- Spring-loaded for self-opening action.
- Handy closure lock for convenient storage.
- Holes for looping and bending wire.
- Handle tip identifies size of cable.



1012

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM-B Cable	Weight (lbs.)
1012	yellow/grey with marking 12/2 at tip	6-1/4" (159 mm)	12 AWG solid (2.5 mm ²)	12/2	.26
1014	yellow/white with marking 14/2 at tip	6-1/4" (159 mm)	14 AWG solid (1.5 mm ²)	14/2	.26

All dimensions are in inches and (millimeters).

⚠WARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

⚠WARNING: Never use on or near live electrical circuits.

⚠WARNING: Always wear approved eye protection.

Strippers, Cutters & Crimpers

