



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 14151RD07 10' Pol R/A Reflex DC Conn DK *Eaton Corp*

Catalog Number	14151RD07
Manufacturer	Eaton Corp
Description	Eaton Oem Prism 18MM Tubular Photoelectric Sensor, Right Angle, Dist 10 FT., Iso SS Relay, 80 Ma At 132 Vac/110 Ma At 132VDC, 4 Pin M12 Connector, 10-30 VDC Input, Current Limited For Loads > 32V Ac/DC, Polarized Retroreflective
Weight per unit	1,313.0 (lbs/each)
Product Category	Photoelectric Sensors

### Features

connection	4-pin M12 connector
dimensions	0.4700 IN X 0.7100 IN X 2.7500 IN

### Descriptions

Description	10' POL R/A REFLEX DC CONN DK
extra long description	ETN 14151RD07 10' POL R/A REFLEX DC
Features	Prism series 18 mm tubular sensors provide a flexible isolated output and twice the optical gain of other sensors in this product class. These cost-effective sensors offer forward- and right-angle viewing models that feature identical gain and optical characteristics for the best fit.
Long Description	Eaton OEM Prism 18mm tubular photoelectric sensor, Right Angle, dist 10 Ft., Iso SS Relay, 80 mA at 132 Vac/110 mA at 132Vdc, 4 Pin M12 Connector, 10-30 Vdc input, Current Limited for loads > 32V AC/DC, Polarized Retroreflective
Product Type	10' Pol R/A Reflex DC Conn DK

### Manufacturer Information

Brand	Eaton
GTIN	00782113011240
Manufacturers Part Number	14151RD07
UPC	782113011240

### Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

### Packaging

Carton	1
Weight Per each	1313



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Vehicles: On-Road - PickUp & Delivery: Food .....
Operating Temperature .....	-13° to 131°F (-25° to 55°C) .....
standard .....	cUL Recognized,UL Recognized,CE Marked .....