



|          |            |      |       |       |       |
|----------|------------|------|-------|-------|-------|
| 149      | 4"         | 9.25 | 12.50 | 3.682 | 4.717 |
| 148      | 3 1/2"     | 9.25 | 12.50 | 3.410 | 4.442 |
| 147      | 3"         | 8.00 | 10.50 | 2.930 | 3.975 |
| 146      | 2 1/2"     | 7.80 | 9.74  | 2.587 | 3.527 |
| 145      | 2"         | 6.00 | 6.62  | 1.878 | 2.660 |
| 144      | 1 1/2"     | 4.34 | 4.85  | 1.686 | 2.635 |
| 143      | 1 1/4"     | 3.37 | 4.25  | 1.393 | 2.334 |
| 142      | 1"         | 3.11 | 3.62  | 1.065 | 2.109 |
| 141      | 3/4"       | 2.72 | 3.12  | .860  | 1.870 |
| 140      | 1/2"       | 2.60 | 2.68  | .595  | 1.590 |
| PART NO. | TRADE SIZE | "A"  | "B"   | MIN   | MAX   |