

### BI-METAL SHIP AUGER BITS

Tougher than Nails

**EXTREME DURABILITY**

High speed steel cutting edge for superior durability in nail-embedded wood

**LONGER LIFE**

High speed steel screw tip increases wear resistance for extended life

**FAST, EASY DRILLING**

Unique parabolic screw tip pulls the bit through material quickly and effortlessly

**RESHARPENABLE**

Resharpener with LENOX Diamond File product no. 25312DIAF1




Our bi-metal technology fuses two premium steels together.



High Speed Steel Screw Tip



Cuts Nails



High Speed Steel Cutting Edge



	1 PER PACK PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
		7-1/2" SHIP AUGER BITS					
1455507A1016	5/8	16	7-1/2	191	4	102	
1455607A1116	11/16	18	7-1/2	191	4	102	
1455707A1216	3/4	19	7-1/2	191	4	102	
1455807A1316	13/16	21	7-1/2	191	4	102	
1455907A1416	7/8	22	7-1/2	191	4	102	
1456007A1516	15/16	24	7-1/2	191	4	102	
1456107A1616	1	25	7-1/2	191	4	102	
1456207A1716	1-1/16	27	7-1/2	191	4	102	
1456307A1816	1-1/8	29	7-1/2	191	4	102	
1456407A2016	1-1/4	32	7-1/2	191	4	102	
1456507A2216	1-3/8	35	7-1/2	191	4	102	
1456607A2416	1-1/2	38	7-1/2	191	4	102	



	1 PER BOX PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
		18" SHIP AUGER BITS					
145390080616*	3/8	10	18	457	12	305	
145400080716*	7/16	11	18	457	12	305	
145410080816	1/2	13	18	457	12	305	
145420080916	9/16	14	18	457	12	305	
145430081016	5/8	16	18	457	12	305	
145440081116	11/16	18	18	457	12	305	
145450081216	3/4	19	18	457	12	305	
145460081316	13/16	21	18	457	12	305	
145470081416	7/8	22	18	457	12	305	
145480081516	15/16	24	18	457	12	305	
145490081616	1	25	18	457	12	305	
145500081716	1-1/16	27	18	457	12	305	
145510081816	1-1/8	29	18	457	12	305	
145520082016	1-1/4	32	18	457	12	305	
145530082216	1-3/8	35	18	457	12	305	
145540082416	1-1/2	38	18	457	12	305	

\*3/8" shank—all others 1/2" shank



**31700K31700**

**16 PIECE, LENOX LEADER® / AUGER KIT**

Augers: 7/8", 1-1/8", 1-1/4". Length: 7-1/2"  
 LENOX LEADER bits: 1-1/2", 1-3/4", 2-1/8", 2-9/16"  
 Extension: 5-1/2". Five lead screws  
 Slim Taper File. Hex Wrench Set  
 LARGE KIT

### BI-METAL SHIP AUGER BITS

Tougher than Nails

#### EXTREME DURABILITY

High speed steel cutting edge for superior durability in nail-embedded wood

#### LONGER LIFE

High speed steel screw tip increases wear resistance for extended life

#### FAST, EASY DRILLING

Unique parabolic screw tip pulls the bit through material quickly and effortlessly

#### RESHARPENABLE

Resharpener with LENOX Diamond File product no. 25312DIAF1



Our bi-metal technology fuses two premium steels together.



High Speed Steel Screw Tip



Cuts Nails



High Speed Steel Cutting Edge



	1 PER PACK PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
		7-1/2" SHIP AUGER BITS					
1455507A1016	5/8	16	7-1/2	191	4	102	
1455607A1116	11/16	18	7-1/2	191	4	102	
1455707A1216	3/4	19	7-1/2	191	4	102	
1455807A1316	13/16	21	7-1/2	191	4	102	
1455907A1416	7/8	22	7-1/2	191	4	102	
1456007A1516	15/16	24	7-1/2	191	4	102	
1456107A1616	1	25	7-1/2	191	4	102	
1456207A1716	1-1/16	27	7-1/2	191	4	102	
1456307A1816	1-1/8	29	7-1/2	191	4	102	
1456407A2016	1-1/4	32	7-1/2	191	4	102	
1456507A2216	1-3/8	35	7-1/2	191	4	102	
1456607A2416	1-1/2	38	7-1/2	191	4	102	



	1 PER BOX PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
		18" SHIP AUGER BITS					
145390080616*	3/8	10	18	457	12	305	
145400080716*	7/16	11	18	457	12	305	
145410080816	1/2	13	18	457	12	305	
145420080916	9/16	14	18	457	12	305	
145430081016	5/8	16	18	457	12	305	
145440081116	11/16	18	18	457	12	305	
145450081216	3/4	19	18	457	12	305	
145460081316	13/16	21	18	457	12	305	
145470081416	7/8	22	18	457	12	305	
145480081516	15/16	24	18	457	12	305	
145490081616	1	25	18	457	12	305	
145500081716	1-1/16	27	18	457	12	305	
145510081816	1-1/8	29	18	457	12	305	
145520082016	1-1/4	32	18	457	12	305	
145530082216	1-3/8	35	18	457	12	305	
145540082416	1-1/2	38	18	457	12	305	

\*3/8" shank—all others 1/2" shank



#### 31700K31700

#### 16 PIECE, LENOX LEADER® / AUGER KIT

Augers: 7/8", 1-1/8", 1-1/4". Length: 7-1/2"  
 LENOX LEADER bits: 1-1/2", 1-3/4", 2-1/8", 2-9/16"  
 Extension: 5-1/2". Five lead screws  
 Slim Taper File. Hex Wrench Set  
 LARGE KIT