



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



18057 1/2"X36"W1 Water Hardening Diamond Dri *Newell (Dymo)*

Catalog Number	18057
Manufacturer	Newell (Dymo)
Description	Heat Shrink Tube Label, Heat Type; Polyolefin Material; Black On White Color; 1.5 Meter; UL 224 Approval; 600 Volt Voltage Rating; 0.5 Millimeter Thickness; 257 Deg F Temperature Rating; 3:1 Shrink Ratio; Rohs Compliant; Tube Width 3/4 Inch
Weight per unit	2.0 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Material	Polyolefin
Shrink Ratio	3:1
Voltage Rating	600 Volt

Material, Color, and Finish

Color	Black on White
-------	----------------

Dimensions and Weight

Length	1.5 Meter
Thickness	0.5 Millimeter

Descriptions

Additional Information	RoHS Compliant; Tube Width 3/4 Inch; Applicable Standard MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5
Commodity Description	Markers & Marking Tapes
Description	1/2"X36"W1 WATER HARDENING DIAMOND DRI
extra long description	HEAT TYPE; BLACK ON WHITE COLOR; UL 224 APPROVAL; 3:1 SHRINK RATIO; TUBE WIDTH 3/4 INCH; APPLICABLE STANDARD ROHS, MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5
Long Description	HEAT SHRINK TUBE LABEL, HEAT TYPE; POLYOLEFIN MATERIAL; BLACK ON WHITE COLOR; 1.5 METER; UL 224 APPROVAL; 600 VOLT VOLTAGE RATING; 0.5 MILLIMETER THICKNESS; 257 DEG F TEMPERATURE RATING; 3:1 SHRINK RATIO; ROHS COMPLIANT; TUBE WIDTH 3/4 INCH
Product Type	Heat Shrink Tube Label

Manufacturer Information

Brand	Newell (Dymo)
GTIN	00071701180575
Manufacturers Part Number	78418055
UPC	071701180575



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description HEAT/COLD SHRINK

Type HEAT

Packaging

Carton 1

Weight Per each 2

Uses, Certifications, and Standards

Approval UL 224

Temperature Rating 257 Deg F