

#184 Flexible Duct



Product Description

Model 184 is a flexible duct with factory installed insulation and vapor barrier. Manufactured in sizes from 4" through 20" in 25 foot lengths and compactly packaged to reduce storage space and ease handling. Our flexible duct offers great versatility and substantial savings in installation time and initial cost. Available in bags or box.

Model 184 Flexible Duct Components

Internal Core (Duct) Material:

Polyester (Manufactured to ASTM Specifications)

Internal Core Reinforcement:

High Carbon, Hard Drawn, Spring Steel Wire (Manufactured to ASTM Specifications)

Insulation:

Fiber Glass Wool, Continuous Blanket, Thermal Resistance (R-Value) (Test Method, ASTM C 518)

Vapor Barrier:

Metalized Polyester with Fiberglass Yarn Reinforcement

Surface Burn Characteristics:

Flame Spread: 25 or less
Smoke Developed: 50 or less
(Test Method: UL procedure 723)

Maximum Positive Pressure: 10" Water Column
Maximum Negative Pressure: 0.5" Water Column
Water Vapor Permeance 0.17 grains per sq. ft. per hour per inch of Hg. (Test Method: ASTM E 96, Procedure A)

Submittal Approval:

Job: _____
Location: _____
Engineer _____

PO No: _____
Job No: _____
Representative: _____

APPROVED for CONSTRUCTION:

By: _____ Title: _____ Date: _____

4200 I 45, P.O. Box 1320, Ennis, TX 75120 Tel. (972) 875-5884 Fax (972) 875-0308
7951 East Evans Rd., San Antonio, TX 78266 Tel. (210) 651-5305 Fax (210) 651-5660

#184 Flexible Duct



Product Description

Model 184 is a flexible duct with factory installed insulation and vapor barrier. Manufactured in sizes from 4" through 20" in 25 foot lengths and compactly packaged to reduce storage space and ease handling. Our flexible duct offers great versatility and substantial savings in installation time and initial cost. Available in bags or box.

Model 184 Flexible Duct Components

Internal Core (Duct) Material:

Polyester (Manufactured to ASTM Specifications)

Internal Core Reinforcement:

High Carbon, Hard Drawn, Spring Steel Wire (Manufactured to ASTM Specifications)

Insulation:

Fiber Glass Wool, Continuous Blanket, Thermal Resistance (R-Value) (Test Method, ASTM C 518)

Vapor Barrier:

Metalized Polyester with Fiberglass Yarn Reinforcement

Surface Burn Characteristics:

Flame Spread: 25 or less
Smoke Developed: 50 or less
(Test Method: UL procedure 723)

Maximum Positive Pressure: 10" Water Column
Maximum Negative Pressure: 0.5" Water Column
Water Vapor Permeance 0.17 grains per sq. ft. per hour per inch of Hg. (Test Method: ASTM E 96, Procedure A)

Submittal Approval:

Job: _____
Location: _____
Engineer _____

PO No: _____
Job No: _____
Representative: _____

APPROVED for CONSTRUCTION:

By: _____ Title: _____ Date: _____

4200 I 45, P.O. Box 1320, Ennis, TX 75120 Tel. (972) 875-5884 Fax (972) 875-0308
7951 East Evans Rd., San Antonio, TX 78266 Tel. (210) 651-5305 Fax (210) 651-5660