

Eaton 1MCB1600RBCA600

Catalog Number: 1MCB1600RBCA600

Eaton main circuit breaker, 1600A, Copper, NEMA 3R, Underground, RGH, Three-wire, Single-phase, 120/240V, (6) #2 AWG-600 kcmil



Photo is representative

General specifications

Product Name

Eaton main circuit breaker

Catalog Number

1MCB1600RBCA600

UPC

786685960074

Product Length/Depth

18.13 in

Product Height

57.13 in

Product Width

25.13 in

Product Weight

314 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

Product specifications

Amperage Rating

1600 A

Bus material

Copper

Feed type

Bottom

Phase

Single-phase

Voltage rating

120/240 V

Enclosure

NEMA 3R

Main circuit breaker

RGH

Number of wires

3

Wire size

(6) #2 AWG-600 kcmil

Resources

Specifications and datasheets

[Eaton Specification Sheet - 1MCB1600RBCA600](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton 1MCB1600RBCA600

Catalog Number: 1MCB1600RBCA600

Eaton main circuit breaker, 1600A, Copper, NEMA 3R, Underground, RGH, Three-wire, Single-phase, 120/240V, (6) #2 AWG-600 kcmil



Photo is representative

General specifications

Product Name

Eaton main circuit breaker

Catalog Number

1MCB1600RBCA600

UPC

786685960074

Product Length/Depth

18.13 in

Product Height

57.13 in

Product Width

25.13 in

Product Weight

314 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

Product specifications

Amperage Rating

1600 A

Bus material

Copper

Feed type

Bottom

Phase

Single-phase

Voltage rating

120/240 V

Enclosure

NEMA 3R

Main circuit breaker

RGH

Number of wires

3

Wire size

(6) #2 AWG-600 kcmil

Resources

Specifications and datasheets

[Eaton Specification Sheet - 1MCB1600RBCA600](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)