

GFCIs Specification Grade Dead Front 20A, 125VAC

Ordering Information

Catalog Number	Rating A.	VAC	Color
Dead Front GFCIs — 1 1/2 HP Rating			
2084-I	20	125	Ivory
2084-W	20	125	White
2084-BK	20	125	Black
2084-LA	20	125	Light Almond




For more information on these and other P&S products refer to our Product Guide or visit our web site.

2084

Circuit protection for locations where a receptacle isn't needed.

Like all P&S GFCIs, this dead front model provides SafeLock™ Protection in addition to improved resistance to surge, corrosion and electrical power line noise. It also features screw-pressure-plate back wiring to speed installation, as well as impact-resistant construction for long, dependable service.



Features & Benefits

GFCIs with SafeLock Protection:

If critical components are damaged and ground fault protection is lost, power to the load is disconnected.

Extra-long strap for better sheet rock contact eliminates "floaters" yet takes standard wall plate.

Trip indicator light (red lamp) makes it easy to identify tripped condition.

Side or internal screw-pressure-plate back wire termination with #14 – #10 AWG stranded or solid, copper or copper-clad conductors.

Captive screws make for easier installation.

Grooved channel and back wire clamp allow for fast installation of ground wires.


Prevents line-load reversal miswire: If miswired, GFCI cannot be RESET.

Two back wire holes per termination add wiring flexibility, eliminate pigtail and save box space.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Line and load terminals backed-out, ready-to-wire.

Improved resistance to surge, corrosion and electrical power line noise.



Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

GFCIs Specification Grade Dead Front 20A, 125VAC

Ordering Information

Catalog Number	Rating A.	VAC	Color
Dead Front GFCIs — 1 1/2 HP Rating			
2084-I	20	125	Ivory
2084-W	20	125	White
2084-BK	20	125	Black
2084-LA	20	125	Light Almond




For more information on these and other P&S products refer to our Product Guide or visit our web site.

2084

Circuit protection for locations where a receptacle isn't needed.

Like all P&S GFCIs, this dead front model provides SafeLock™ Protection in addition to improved resistance to surge, corrosion and electrical power line noise. It also features screw-pressure-plate back wiring to speed installation, as well as impact-resistant construction for long, dependable service.



Features & Benefits

GFCIs with SafeLock Protection:

If critical components are damaged and ground fault protection is lost, power to the load is disconnected.

Extra-long strap for better sheet rock contact eliminates "floaters" yet takes standard wall plate.

Trip indicator light (red lamp) makes it easy to identify tripped condition.

Side or internal screw-pressure-plate back wire termination with #14 – #10 AWG stranded or solid, copper or copper-clad conductors.

Captive screws make for easier installation.

Grooved channel and back wire clamp allow for fast installation of ground wires.


Prevents line-load reversal miswire: If miswired, GFCI cannot be RESET.

Two back wire holes per termination add wiring flexibility, eliminate pigtailing and save box space.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Line and load terminals backed-out, ready-to-wire.

Improved resistance to surge, corrosion and electrical power line noise.



2084-LA

Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling