



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097TRI Radiant Self Test TR Gfci 20A 125V Iv *Pass & Seymour/Legrand*

| | |
|------------------|---|
| Catalog Number | 2097TRI |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Ivory, 0.025 Sec Trip Time, Tamper Resistant, 0.2800 LB |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|------------------------|
| actuator | Control Circuit |
| amperage rating | 20 |
| connection | Back and side wire |
| indoor/outdoor | Indoor |
| interrupt rating | 4 to 6 mA |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Number of Wires | 3 |
| Outlet Type | Tamper-Resistant, GFCI |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wall Plate Included | YES |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|------|
| Length | 1.03 |
| Width | 1.73 |

Descriptions

| | |
|------------------------|---------------------------------------|
| Description | RADIANT SELF TEST TR GFCI 20A 125V IV |
| extra long description | P&S 2097TRI RADIANT SELF TEST TR GF |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007036275 |
| UPC | 785007036275 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Residential GFCI devices |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.275 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------------------|
| environmental conditions | 95% Humidity, UL 94 V2 |
| Operating Temperature | -35°C to +66°C |
| standard | CULUS, UL, cULus, UL Listed, FSUL |