



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street  
88201-0000, NM Roswell  
Phone: 575-208-1571  
Fax: 575-208-1572



## 20MR16FL35C(BAB) 20W MR16 Lamp

*Sylvania-Ledvance*

Catalog Number	20MR16FL35C(BAB)
Manufacturer	Sylvania-Ledvance
Description	Tungsten Halogen Tru Aim MR16 Standard Axial Filament Uv Filter Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20WATT 12VOLT Flood Beam
Weight per unit	0.0900 (lbs/each)
Product Category	Halogen Reflector Ar, BR, JDR,

### Features

average life	2000
Base	GU5.3 Bipin
beam angle	36
dimmable	Yes
lumens	250
Shape	MR16
start type	Instant
Voltage	12.00 V
Voltage Rating	12
Wattage	20

### Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000
Finish	Covered

### Descriptions

Description	20W MR16 LAMP
extra long description	SYL 20MR16FL35CBAB-12V/54306 20MR16
Long Description	Tungsten Halogen Tru Aim MR16 STANDARD Axial Filament UV Filter Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20Watt 12Volt Flood Beam
Product Type	20MR16FL35CBAB 12V 20/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135543067
Manufacturers Part Number	20MR16/FL35/C(BAB)-12V/54306
UPC	046135543067



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street  
88201-0000, NM Roswell  
Phone: 575-208-1571  
Fax: 575-208-1572

## Taxonomies, Classifications, and Categories

Category Description INCANDESCENT

Type HALOGEN

## Packaging

Carton 1

Package 20

Weight Per each 0.09

## Uses, Certifications, and Standards

Application Medium Screwbase or bi-pin

standard BAB