



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



222413 LN Splicing Connector, 3COND, 28-12 Awg, Gy Wago Corporation

| | |
|------------------|---|
| Catalog Number | 222413 |
| Manufacturer | Wago Corporation |
| Description | Splicing Connector, Aluminum;Copper Conductor Material, Non-Insulated, Gray Insulation Color, Made In Usa, 12 Awg;2.5 MM^2 Maximum Conductor Size, +85 °C Maximum Operating Temperature, 400 V Maximum Voltage Rating, 0.08 MM^2;28 Awg Minimum Conductor Size, +40 °C Minimum Operating Temperature, 0.571 In;14.5 MM Overall Length, UI International Germany GMBH;UI Underwriters Laboratories Inc Standards Met, 2-Conductor Terminal Terminal Type, 4.283 G Weight |
| Weight per unit | 0.4721 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Descriptions

| | |
|-------------|---|
| Description | LN SPLICING CONNECTOR, 3COND, 28-12 AWG, GY |
|-------------|---|

Manufacturer Information

| | |
|---------------------------|-------------------|
| Manufacturers Part Number | 222-413/K194-4045 |
|---------------------------|-------------------|

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | Residential cord connectors |
|----------------------|-----------------------------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 0.4721 |