

Market focused portfolio with products designed for broad applications

Value - competitive prices with industry-leading DLC listings

Performance - market leading performance with connected sensors options delivering value beyond lumens per watt






Whether lighting schools, offices, or hospitals on a budget, Metalux's commercial recessed products offer a complete family of innovative, affordable, and energy saving LED solutions for your next project.

Click on products to learn more

Good

Better

Best

								
		GR8 Fluorescent	FP LED	AP GR	GR LED	RTC LED	FR LED Standard	FR LED High Perf.
APPLICABILITY ¹	Education	★	★★★	★★★	★★★	★★★	★★	★★
	Office	★	★★	★★	★★	★★★	★★★	★★★
	Healthcare	★	★	★★	★★	★★	★★	★★
	Retail	★	★★★	★★	★★	★★	★★	★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	2x2, 2x4	
	lm/W (Max)	< 90 (depends on lamp and ballast)	124	140	140	126	130	150
	Lum (Max)	9000	7000	6400	18000	7000	3200	8000
	Life (@60K)	L10	L73	L90	L89	L75	L88	
	Lens	Clear, Prismatic	Frost, Smooth	Clear, Prismatic	Frost, Prismatic	Frost, Ribbed	Frost, Smooth	
	Emergency	Integrated	Integrated	No	Integrated	Integrated	Integrated	
	CRI	70 or 80 (depending on lamp selected)	80 / 90	80+	80+	80+	80+	
	Sensor Location	None	Tile Mount	Tile Mount	Integrated	Integrated	Integrated	
	DLC	None	Standard	Premium	Premium	Premium	Premium	
	Door	Yes	No	Yes	Yes	No	Yes	
INTERGRATED CONTROLS	Basic Occupancy				✓	✓	✓	✓
	Stand Alone Daylight / Occupancy				✓	✓	✓	✓
	WaveLinX				✓	✓	✓	✓
	LumaWatt Pro				✓	✓	✓	✓
	DLVP				✓	✓	✓	✓

Notes: 1. ★★ = high applicability, ★ = medium applicability, ★ = low applicability, blank = non-applicable

Market focused portfolio with products designed for broad applications

Value - competitive prices with industry-leading DLC listings

Performance - market leading performance with connected sensors options delivering value beyond lumens per watt







Whether lighting schools, offices, or hospitals on a budget, **Metalux's** commercial recessed products offer a complete family of innovative, affordable, and energy saving LED solutions for your next project.

Click on products to learn more

Good

Better

Best

								
		GR8 Fluorescent	FP LED	AP GR	GR LED	RTC LED	FR LED Standard	FR LED High Perf.
APPLICABILITY	Education	★	★★★	★★★	★★★	★★★	★★	★★
	Office	★	★★	★★	★★	★★★	★★★	★★★
	Healthcare	★	★	★★	★★	★★	★★	★★
	Retail	★	★★★	★★	★★	★★	★★	★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	2x2, 2x4	
	lm/W (Max)	< 90 <small>(depends on lamp and ballast)</small>	124	140	140	126	130	150
	Lum (Max)	9000	7000	6400	18000	7000	3200	8000
	Life (@60K)	L10	L73	L90	L89	L75	L88	
	Lens	Clear, Prismatic	Frost, Smooth	Clear, Prismatic	Frost, Prismatic	Frost, Ribbed	Frost, Smooth	
	Emergency	Integrated	Integrated	No	Integrated	Integrated	Integrated	
	CRI	70 or 80 <small>(depending on lamp selected)</small>	80 / 90	80+	80+	80+	80+	
	Sensor Location	None	Tile Mount	Tile Mount	Integrated	Integrated	Integrated	
	DLC	None	Standard	Premium	Premium	Premium	Premium	
	Door	Yes	No	Yes	Yes	No	Yes	
INTEGRATED CONTROLS	Basic Occupancy				✓	✓	✓	✓
	Stand Alone Daylight / Occupancy				✓	✓	✓	✓
	WaveLinX				✓	✓	✓	✓
	LumaWatt Pro				✓	✓	✓	✓
	DLVP				✓	✓	✓	✓

Notes: 1. ★★ = high applicability, ★ = medium applicability, ★ = low applicability, blank = non-applicable