

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460079](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite Plug with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130146](#)
 IP Rating IP67
 NEMA Configuration NEMA L7-15
 Overview [Watertite® Wet-Location Wiring Solutions](#)
 Product Literature Order No 987650-8067
 Product Name Watertite
 Receptacle Type N/A
 Specialty N/A
 Type Plug
 UPC 78678871204
 Woodhead Yes

Physical

Cord Grip Body Size F2 1/2"
 Flange No
 Flip Lid No
 Gender Male
 Length N/A
 Locking Blade Yes
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 277V

Material Info

Engineering Number 24W34



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130146 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460079](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite Plug with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130146](#)
 IP Rating IP67
 NEMA Configuration NEMA L7-15
 Overview [Watertite® Wet-Location Wiring Solutions](#)
 Product Literature Order No 987650-8067
 Product Name Watertite
 Receptacle Type N/A
 Specialty N/A
 Type Plug
 UPC 78678871204
 Woodhead Yes

Physical

Cord Grip Body Size F2 1/2"
 Flange No
 Flip Lid No
 Gender Male
 Length N/A
 Locking Blade Yes
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 277V

Material Info

Engineering Number 24W34



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Relevant

RoHS Phthalates Not Reviewed

Search Parts in this Series

[130146 Series](#)