



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 250SRTI 1/2" Ins Steel Emt Raintight Compression Conn *Bridgeport Fittings*

Catalog Number	250SRTI
Manufacturer	Bridgeport Fittings
Description	Compression Connector, 1/2 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 1-3/4 In Length, 1-1/32 In Diameter, +105 °C Operating Temperature, 0.0006 LB/Ea
Weight per unit	0.0006 (lbs/each)
Product Category	Steel Insulated Straight Compr

### Features

Connector Type	Steel Raintight/Concrete-Tight Insulated
insulation	Insulated Throat
media	Yes

### Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

### Dimensions and Weight

Size	1/2
------	-----

### Descriptions

Description	1/2" INS STEEL EMT RAIN TIGHT COMPRESSION CONN
extra long description	BPT 250-SRTI 1/2" STEEL RAIN TIGHT C

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747122506
UPC	781747122506

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

### Packaging

Carton	25
Package	250
Weight Per each	0.0006

### Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight/Raintight. Insulated Throat - 105°C. Patented
standard	cULus