



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 252DCI2 1" Diecast Emt Insulated Concrete Tight Conn

*Bridgeport Fittings*

|                  |   |
|------------------|---|
| Catalog Number   | 252DCI2   |
| Manufacturer     | Bridgeport Fittings   |
| Description      | Emt Concrete Tight Connector, 1 In Trade Size, Die-Cast Zinc Material, Insulated, 15/16 In Length, 1-11/16 In Diameter, +105 °C Operating Temperature, 0.1590 LB/Ea |
| Weight per unit  | 0.1590 (lbs/each)   |
| Product Category | Die Cast Insulated Straight CO  |

### Features

|                |                  |
|----------------|------------------|
| Connector Type | Compression      |
| insulation     | Insulated Throat |
| media          | Yes              |

### Material, Color, and Finish

|        |              |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

### Dimensions and Weight

|      |   |
|------|---|
| Size | 1 |
|------|---|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 1" DIECAST EMT INSULATED CONCRETE TIGHT CONN |
| extra long description | BPT 252-DCI2 1" COMP. CONN. INS. ZI          |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Bridgeport     |
| GTIN  | 00781747162526 |
| UPC   | 781747162526   |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | DIECAST EMT FITTINGS |
| Type                 | CONNECTOR            |

### Trade Size

|            |   |
|------------|---|
| Trade Size | 1 |
|------------|---|

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 15    |
| Package         | 150   |
| Weight Per each | 0.159 |

### Uses, Certifications, and Standards

|          |         |
|----------|---------|
| standard | UL, CSA |
|----------|---------|