



259I 4" Ins Steel Emt Compression Connector

Nsi Industries

Catalog Number	259I
Manufacturer	Nsi Industries
Description	Emt Compression Connector, 4 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 4-23/32 In Length, 5-1/8 In Diameter, +105 °C Operating Temperature, 0.5167 LB/Ea.
Weight per unit	0.5167 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Compression
insulation	Insulated Throat
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	4
------	---

Descriptions

Description	4" INS STEEL EMT COMPRESSION CONNECTOR
extra long description	BPT 259-I 4 IN Steel Ins Comp Conn.

Manufacturer Information

Brand	Bridgeport
GTIN	00781747102591
UPC	781747102591

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	4
------------	---

Packaging

Carton	6
Weight Per each	0.5167

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight.
standard	cULus