





GE
Lighting

12983 - 25G25 6PK

GE crystal clear 25 watt G25 1-pack

- Add a decorative touch by using GE Crystal Clear bulbs in chandeliers, sconces or anywhere the bulb is visible.
- Add sparkle to your decorative fixtures with GE crystal clear bulbs. The clear glass and elegant filament design provide a decorative touch in fixtures where the bulb is visible. And, GE crystal clear globes' decorative round shape is perfect for illuminating pendant and vanity fixtures
- G25 globe with medium base for use in vanity strips
- Lasts 1.4 years based on 3 hours per day usage
- 190 lumens providing subtle, reassuring™ light
- 2500K soft white light appearance
- Estimated yearly energy costs \$3.01 based on 3 hours per day \$0.11 per kWh



GENERAL CHARACTERISTICS

Lamp Type	Incandescent - Decorative
Bulb	G25
Base	Medium Screw (E26)
Filament	CC-6
Bulb Finish	Clear
Rated Life (Vert)	1500.0 h
Rated Life	1500.0 hrs
Bulb Material	Soft glass
Primary Application	Globe

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	190.0
Color Temperature	2500.0 K

ELECTRICAL CHARACTERISTICS

Wattage	25.0
Voltage	120.0

DIMENSIONS

Maximum Overall Length (MOL)	4.5000 in(114.3 mm)
Bulb Diameter (DIA)	3.125 in(79.4 mm)

PRODUCT INFORMATION

Product Code	12983
Description	25G25 6PK
Standard Package	Case
Standard Package GTIN	00043168129831
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168908825





GE
Lighting

12983 - 25G25 6PK

GE crystal clear 25 watt G25 1-pack

- Add a decorative touch by using GE Crystal Clear bulbs in chandeliers, sconces or anywhere the bulb is visible.
- Add sparkle to your decorative fixtures with GE crystal clear bulbs. The clear glass and elegant filament design provide a decorative touch in fixtures where the bulb is visible. And, GE crystal clear globes' decorative round shape is perfect for illuminating pendant and vanity fixtures
- G25 globe with medium base for use in vanity strips
- Lasts 1.4 years based on 3 hours per day usage
- 190 lumens providing subtle, reassuring™ light
- 2500K soft white light appearance
- Estimated yearly energy costs \$3.01 based on 3 hours per day \$0.11 per kWh



GENERAL CHARACTERISTICS

Lamp Type	Incandescent - Decorative
Bulb	G25
Base	Medium Screw (E26)
Filament	CC-6
Bulb Finish	Clear
Rated Life (Vert)	1500.0 h
Rated Life	1500.0 hrs
Bulb Material	Soft glass
Primary Application	Globe

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	190.0
Color Temperature	2500.0 K

ELECTRICAL CHARACTERISTICS

Wattage	25.0
Voltage	120.0

DIMENSIONS

Maximum Overall Length (MOL)	4.5000 in(114.3 mm)
Bulb Diameter (DIA)	3.125 in(79.4 mm)

PRODUCT INFORMATION

Product Code	12983
Description	25G25 6PK
Standard Package	Case
Standard Package GTIN	00043168129831
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168908825