

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460095](#)

**Status:** **Active**

**Overview:** [Watertite® Wet-Location Wiring Solutions](#)

**Description:** Watertite Connector with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

|     |        |
|-----|--------|
| CSA | LR6837 |
| UL  | E10176 |

**General**

|                             |  |
|-----------------------------|--|
| Product Family              | Wiring Devices   |
| Series                      | <a href="#">130146</a>                                   |
| IP Rating                   | IP67   |
| NEMA Configuration          | NEMA L7-15   |
| Overview                    | <a href="#">Watertite® Wet-Location Wiring Solutions</a> |
| Product Literature Order No | 987650-8067  |
| Product Name                | Watertite  |
| Receptacle Type             | Single   |
| Specialty                   | N/A  |
| Type                        | Connector  |
| UPC                         | 78678871304  |
| Woodhead                    | Yes  |

**Physical**

|                     |               |
|---------------------|---------------|
| Cord Grip Body Size | F2 1/2"       |
| Flange              | No            |
| Flip Lid            | No            |
| Gender              | Female        |
| Length              | N/A           |
| Locking Blade       | Yes           |
| Poles               | 2-pole/3-wire |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Cord Type                     | N/A   |
| Current - Maximum per Contact | 15.0A |
| GFCI                          | No    |
| Lighted Connector             | No    |
| Voltage - Maximum             | 277V  |

**Material Info**

|                    |       |
|--------------------|-------|
| Engineering Number | 25W34 |
|--------------------|-------|



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Relevant |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130146 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460095](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E10176

**General**

Product Family      Wiring Devices  
 Series      [130146](#)  
 IP Rating      IP67  
 NEMA Configuration      NEMA L7-15  
 Overview      [Watertite® Wet-Location Wiring Solutions](#)  
 Product Literature Order No      987650-8067  
 Product Name      Watertite  
 Receptacle Type      Single  
 Specialty      N/A  
 Type      Connector  
 UPC      78678871304  
 Woodhead      Yes

**Physical**

Cord Grip Body Size      F2 1/2"  
 Flange      No  
 Flip Lid      No  
 Gender      Female  
 Length      N/A  
 Locking Blade      Yes  
 Poles      2-pole/3-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      15.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      277V

**Material Info**

Engineering Number      25W34



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS      Not Reviewed

ELV      Not Relevant

RoHS Phthalates      Not Reviewed

**Search Parts in this Series**

[130146](#) Series