



Southwire™

TOOLS & EQUIPMENT

PORTABLE GFCI PROGRAM

Safety on the jobsite is paramount to maintaining a productive and injury-free environment. Southwire ShockShield® Ground Fault Circuit Interrupter (GFCI) products are designed to UL standards. Shockshield GFCI's help ensure personal safety from electrical shock while also protecting power tools and power equipment. We incorporate the highest quality components and the latest technology to provide consistent and reliable performance you can count on.

Check out our large selection of standard, convenience and user attachable GFCI's all designed to keep you and your workplace safe.

Manual Reset after GFCI Trip and Power Outage

- Prevents Unattended Tool Restart after Power Loss
- Performs Safe-Start Function

Surge Protection

Test and Reset Buttons for Periodic Testing



14880002-6



14650013-6



25000016-6



26020008-6



28438802



14880023-6



28458802

Southwire Part No.	Gauge	Length (ft.)	Description	Master Pack	Master Wt.	UPC Number	Outlet Configuration	Certifications
28438802	12/3	6	Duplex Outlet Box w/Flip Cover and Inline GFCI	6	14.76	029892028220		cUL US
28458802	12/3	6	Quad Outlet Box w/Flip Cover and Inline GFCI	2	6.10	029892028169		cUL US
14880002-6	18 - 12 AWG	-	Right Angle User Attachable	6	2.40	024098900271	N/A	cUL US
25000016-6	18 - 12 AWG	-	Inline User Attachable	6	3.60	024098901544	N/A	cUL US
14650013-6	-	-	Right Angle GFCI Adapter - Plug in	6	2.40	024098902657		cUL US
14880023-6	12/3	2	Right Angle GFCI Cordset with Tri-Source	6	7.20	024098902718		cUL US
26020008-6	12/3	2	Inline GFCI cordset with Tri-Source	6	8.40	024098902145		cUL US

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



FEATURES & BENEFITS

Right Angle Cordset

14880023-6

- Tri-Source molded T-Head with 3 receptacles
- Rain-proof rated
- 2-foot long 12/3 cord
- Cord lengths available up to 99'
- Lower cost cordset option
- **Applications:** High Pressure Sprayer Washers, Power Tools, Drain Snakes, Pumps, Construction Sites and Industrial Appliances

GFCI Adapter

14650013-6

- Turn any outlet into a GFCI protected outlet
- Fits in an electrician's tool bag
- Single grounded outlet
- Rated for indoor use only
- 314 Joules Surge Protection
- **Applications:** Power Tools, Saws, Drills, Extension Cords and Lighting

Inline Cordset

26020008-6

- Tri-Source molded T-Head with 3 receptacles
- Extra Heavy-Duty 12 /3 Cord
- Rated for outdoor use and rugged construction-type environments
- 2-foot long cord
- Cord lengths available up to 50'
- **Applications:** Construction Sites, Saws and Drills, Portable Electric Power Tools and Multiple Tool Use

User Attachables

14880002-6

- Turn a tool or cord into a GFCI
- Easy attachment
- Rain-proof rated
- Accepts 18-12 awg cord

25000016-6

- Inline GFCI protects downline
- Easy to attach
- Rain-proof rated
- Accepts 18-12 awg cord
- **Applications:** Pressure Washers, Drain Snakes, Floor Cleaners, Industrial Appliances, Power Tools, Pumps, Boat Lifts and Extension Cords

Outlet Box Units

28438802

- Duplex receptacle with inline GFCI
- Spring-loaded outlet cover
- Rugged plastic construction with handle
- 6-Foot 12/3 Cord

28458802

- Quad (4) receptacles with inline GFCI
- Spring-loaded outlet covers
- Rugged plastic construction with handle
- 6-Foot 12/3 Cord
- **Applications:** Drills, Saws, Lathes, Lighting, Multiple Tools and Construction Sites