



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2623GRY SW Dec 3W 20A 120/277V Grounded Gy

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 2623GRY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 3-Way, Back and Side-Wire, Decorator Switch, 20A, 120/277V. |
| Weight per unit | 0.2200 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| amperage rating | 20 |
| Contact Rating | 20Amp, 120/277Vac |
| insulation | Bare |
| media | Yes |
| Poles | 3way |
| Voltage Rating | 120/277 |
| Wattage | 3 |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|------|-------|
| Size | 4.25" |
|------|-------|

Descriptions

| | |
|------------------------|---|
| Description | SW DEC 3W 20A 120/277V GROUNDED GY |
| extra long description | P&S 2623GRY SW DEC 3W 20A 120/277V |
| Long Description | 3-way, Back and Side-Wire, Decorator Switch, 20A, 120/277V. |
| Product Type | SW Dec 3W 20A 120/277V Grounded Gy |
| Special Features | Impact resistant polycarb back body & frame, cushioned thermoplastic paddle , unique single rocking butterfly contact |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007539523 |
| Manufacturers Part Number | 2623-GRY |
| UPC | 785007539523 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | SWITCH |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.22 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|------------------|
| Application | Industrial |
| Mounting | WALL |
| standard | UL 20 |