

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301420038](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130142](#)
 IP Rating N/A
 NEMA Configuration NEMA L16-30
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Literature Order No 987650-8068
 Product Name Super-Safeway
 Receptacle Type N/A
 Specialty N/A
 Type Plug
 UPC 78678870434
 Woodhead Yes

Physical

Flange No
 Flip Lid No
 Gender Male
 Length N/A
 Locking Blade Yes
 Poles 3-pole/4-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 3Ø 480V

Material Info

Engineering Number 2876



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130142 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301420038](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130142](#)
IP Rating N/A
NEMA Configuration NEMA L16-30
Overview [Heavy-Duty Industrial Wiring Devices](#)
Product Literature Order No 987650-8068
Product Name Super-Safeway
Receptacle Type N/A
Specialty N/A
Type Plug
UPC 78678870434
Woodhead Yes

Physical

Flange No
Flip Lid No
Gender Male
Length N/A
Locking Blade Yes
Poles 3-pole/4-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 30.0A
GFCI No
Lighted Connector No
Voltage - Maximum 3Ø 480V

Material Info

Engineering Number 2876



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130142 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION