
29W09 WATERTIGHT NEMA 4X/6P LOCKING CONNECTOR

29W09 | [Pass & Seymour](#)



FEATURES & BENEFITS

Watertight Connector, 30amp 3^Y 120/208V, Non-NEMA Configuration, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Connector

Features: Watertight

Number Of Poles: 3

Number Of Wires: 3

Special Features: Watertight, Non-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

CONSTRUCTION INFORMATION

Material 1: Rubber

DIMENSIONS

Diameter (US): 2.76"
Length (US): 4.88"

TECHNICAL INFORMATION

Amps: 30A
Material: Rubber
NEMA Rating: 4X/6P
Volts: 3°Y 120/208V
Volts (AC): 3°Y 120/208V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant



29W09 WATERTIGHT NEMA 4X/6P LOCKING CONNECTOR

29W09 | [Pass & Seymour](#)



FEATURES & BENEFITS

Watertight Connector, 30amp 3^Y 120/208V, Non-NEMA Configuration, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Connector

Features: Watertight

Number Of Poles: 3

Number Of Wires: 3

Special Features: Watertight, Non-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

CONSTRUCTION INFORMATION

Material 1: Rubber

DIMENSIONS

Diameter (US): 2.76"
Length (US): 4.88"

TECHNICAL INFORMATION

Amps: 30A
Material: Rubber
NEMA Rating: 4X/6P
Volts: 3°Y 120/208V
Volts (AC): 3°Y 120/208V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

