

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470105](#)

**Status:** **Active**

**Overview:** [Watertite® Wet-Location Wiring Solutions](#)

**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E10176

**General**

Product Family Wiring Devices  
Series [130147](#)  
IP Rating IP67  
NEMA Configuration NEMA L15-30  
Overview [Watertite® Wet-Location Wiring Solutions](#)  
Product Literature Order No 987650-8067  
Product Name Watertite  
Receptacle Type Single  
Specialty N/A  
Type Connector  
UPC 78678871333  
Woodhead Yes

**Physical**

Cord Grip Body Size F4 1"  
Flange No  
Flip Lid No  
Gender Female  
Length N/A  
Locking Blade Yes  
Poles 3-pole/4-wire

**Electrical**

Cord Type N/A  
Current - Maximum per Contact 30.0A  
GFCI No  
Lighted Connector No  
Voltage - Maximum 3ø 250V

**Material Info**

Engineering Number 29W75



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130147 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470105](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E10176

**General**

Product Family	Wiring Devices
Series	<a href="#">130147</a>
IP Rating	IP67
NEMA Configuration	NEMA L15-30
Overview	<a href="#">Watertite® Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-8067
Product Name	Watertite
Receptacle Type	Single
Specialty	N/A
Type	Connector
UPC	78678871333
Woodhead	Yes

**Physical**

Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	Yes
Poles	3-pole/4-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	3ø 250V

**Material Info**

Engineering Number	29W75
--------------------	-------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
------------	--------------

ELV	Not Relevant
-----	--------------

RoHS Phthalates	Not Reviewed
-----------------	--------------

**Search Parts in this Series**

[130147 Series](#)