

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E10176

**General**

Product Family	Wiring Devices
Series	<a href="#">130147</a>
Exclude SD Check	Yes
IP Rating	IP67
NEMA Configuration	NEMA L16-30
Overview	<a href="#">Watertite Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-8067
Product Name	Watertite
Receptacle Type	Single
Specialty	N/A
Type	Connector
UPC	78678871334

**Physical**

Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	Yes
Net Weight	441.798/g
Poles	3-pole/4-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	3ø 480V

**Material Info**

Engineering Number	29W76
--------------------	-------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E10176

**General**

Product Family                      Wiring Devices  
 Series                                  [130147](#)  
 Exclude SD Check                      Yes  
 IP Rating                                IP67  
 NEMA Configuration                      NEMA L16-30  
 Overview                                [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No              987650-8067  
 Product Name                              Watertite  
 Receptacle Type                          Single  
 Specialty                                 N/A  
 Type                                        Connector  
 UPC                                         78678871334

**Physical**

Cord Grip Body Size                      F4 1"  
 Flange                                      No  
 Flip Lid                                      No  
 Gender                                        Female  
 Length                                        N/A  
 Locking Blade                                Yes  
 Net Weight                                 441.798/g  
 Poles                                         3-pole/4-wire

**Electrical**

Cord Type                                      N/A  
 Current - Maximum per Contact              30.0A  
 GFCI                                         No  
 Lighted Connector                          No  
 Voltage - Maximum                          3ø 480V

**Material Info**

Engineering Number                          29W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)