



## 2RCS10X 12-10 Heat Shrink Butt Splice

Abb Installation Products, Inc

Catalog Number	2RCS10X
Manufacturer	Abb Installation Products, Inc
Description	Heat Shrinkable Butt Splice, Length 1.60 Inches, Width .31 Inches, Maximum Insulation Diameter .250, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated
Weight per unit	0.0090 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

Material	Copper
Voltage Rating	600 V

### Material, Color, and Finish

Color	Yellow
Finish	Electro -Tin Plated

### Descriptions

Description	12-10 HEAT SHRINK BUTT SPLICE
extra long description	ABB 2RCS10X HEAT-SHR BUTT SPLICE 12
Long Description	Heat Shrinkable Butt Splice, Length 1.60 Inches, Width .31 Inches, Maximum Insulation Diameter .250, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated
Product Type	Heat-SHR Butt Splice 12-10 Len 1.6
Special Features	Self-insulated with heat-shrinkable polyolefin and internally coated sealant. Upon completed installation, a fully sealed connection is achieved to protect the joint against the degrading effects of galvanic action, corrosion, and environmental exposure.

### Manufacturer Information

Brand	Sta-Kon
GTIN	00786210703282
Manufacturers Part Number	2RCS10X
UPC	786210703282

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Heat Shrinkable Butt Splice

### Availability

minimum qty	25
-------------	----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	25
Package	125
Weight Per each	0.009

## Uses, Certifications, and Standards

Temperature Rating	150 C
--------------------	-------