

Wraparounds

WPLD Series - High lm/W, DLC, Energy Star and T24



WPLD series is a versatile LED wraparound series with a streamlined, low profile design that displays uniform, soft light at up to 60% energy savings over fluorescent light sources. Mounting slots allow for installation directly into the junction box with 100° of rotational freedom. Features include suspension mount with optional mounting kit, 93 CRI, dimming to 10% and up to 115 lumens per watt. These features make the WPLD series an ideal choice for light commercial or kitchens, garage, basement, bedrooms, office, and bonus rooms.

Construction and performance

- Available in ten different models: 2 ft. up to 2700 and 4 ft. up to 4600 lumens
- Available 120/277 Universal voltage and 120V
- Two Color Temperatures: 3500K and 4000K
- White post-painted cold rolled steel housing with polymer end caps for a finished aesthetic
- Smooth white lens provides uniform, glare-free light output
- Optional 93 CRI LED's for accurate color rendering
- Suitable for ceiling, wall, or suspension mounting
- Phase cut and 0-10V dimming to 10%



Reliability and compliance

- cULus 1598 listed for damp locations
- Five year comprehensive fixture warranty
- LED's projected life of 50,000 hours at 70% lumen output
- Complies with IESNA LM-79 and LM-80 test standards
- 120V models are ENERGY STAR® Certified
- T24 High Efficiency residential compliant model available

Catalog #	UPC	CCT (K)	CRI (Min)	Delivered Lumens	Watts	Efficacy lm/W)	Dimming controls
2WPLD2035R	080083785384	3500	80	2645	23	115	Phase cut
4WPLD4035R	080083785391	3500	80	4577	43	107	Phase cut
2WPLD2040R	080083750627	4000	80	2623	24	110	Phase cut
4WPLD2340R	080083747474	4000	80	2639	24	110	Phase cut
4WPLD3130R9	080083750634	3000	93	3210	37	88	Phase cut
4WPLD3140R9	080083747467	4000	93	3422	36	94	Phase cut
2WPLD2035C	080083750610	3500	80	2476	22	114	0-10V
4WPLD4035C	080083750603	3500	80	4460	39	113	0-10V
2WPLD2040C	080083801367	4000	80	2543	23	110	0-10V
4WPLD4040C	080083749676	4000	80	4603	42	110	0-10V



Powering Business Worldwide

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. SA519027EN
January 10, 2018

Eaton is a registered trademark.
All other trademarks are property of their respective owners.
Product availability, specifications, and compliances are subject to change without notice.