



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



30092J Greenie Grounding Wire Conn, 92 Green, 150/Jar

Ideal

Catalog Number	30092J
Manufacturer	Ideal
Description	Ideal, Grounding Wire Connector, Greenie, Twist-On, Number Of Conductors: 2 to 5, Conductor Range: 14 - 10 Awg, Min 2 - 14, Max 4-12, Color: Green, Material: Polypropylene, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell, Model Number: 92, Width: 29/32 In, Height: 1-5/32 In, Flammability Rating: UI 94V-2
Weight per unit	N/A
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Polypropylene
Voltage Rating	600

Material, Color, and Finish

Color	Green
-------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Descriptions

Description	GREENIE GROUNDING WIRE CONN, 92 GREEN, 150/JAR
extra long description	IDEAL 30-092J GREENIE GROUNDING 92,
Features	The Wing-Nut Wire Connector provides an easy, secure grip when connecting a wide range of wires. The specially designed contoured wings make for extra torque and quick work on any electrical job. The wide range, live-action spring is flexible enough to handle small combinations with ease but then expands to accept large combinations when you need it. It can also be reused on same size or larger combinations for quick and easy circuit changes and additions. The Wing-Nut also features a tough, copolymer, flam
Long Description	IDEAL, Grounding Wire Connector, Greenie, Twist-On, Number Of Conductors: 2 to 5, Conductor Range: 14 - 10 AWG, Min 2 - 14, MAX 4-12, Color: Green, Material: Polypropylene, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell, Model Number: 92, Width: 29/32 IN, Height: 1-5/32 IN, Flammability Rating: UL 94V-2
Product Type	Greenie Grounding 92, 150 Jar
Special Features	Complies With Federal Specification W-S-610E;Contoured Wings For Maximum Leverage;Features: Designed For Making Ground Connections And Bonding Non-Metallic Sheathed Cable;Flammability Rating: UL 94V-2;Height: 1-5/32 IN;Live-Action, Square-Wire Spring Provides Superior Grounding Connections;Model Number: 92;Tough, UL 94V-2 Flame-Retardant Shell;UL Listed To 467 And CSA Certified To C22.2 #188;Width: 29/32 IN

Manufacturer Information

Brand	Ideal
GTIN	00783250541232
Manufacturers Part Number	30-092J
UPC	783250541232

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Twist-On

Availability

minimum qty	150
-------------	-----

Packaging

Carton	150
Package	900
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell
standard	CSA Certified to C22.2 #188, UL Listed to 467, complies with Federal Specification W-S-610E, RoHS Compliant