



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 300MIF130VPK3 \*Delisted\* 300W 130V PS25 Frost Med Base Incand *Ge By Current Lamps*

|                  |   |
|------------------|---|
| Catalog Number   | 300MIF130VPK3   |
| Manufacturer     | Ge By Current Lamps   |
| Description      | A-Line Incandescent Lamp, 2950 K, 6120 LM Brightness (Lumens), 300 W, 130 V, Inside Frost, CC-8 Filament, 750 H Average Life, Medium Base, Non Dimmable, 3.125 In Diameter, 6.93 In Length, 0.22 LB |
| Weight per unit  | 0.2200 (lbs/each)   |
| Product Category | Line A, P, PS Shape Lamps   |

### Features

|                |                    |
|----------------|--------------------|
| Base           | Medium Screw (E26) |
| lumens         | 6120               |
| Voltage Rating | 130                |
| Wattage        | 300                |

### Material, Color, and Finish

|       |              |
|-------|--------------|
| Color | INSIDE FROST |
|-------|--------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | *DELISTED* 300W 130V PS25 FROST MED BASE INCAND |
| extra long description | GEL 300M/IF/130V-PK3 73790 INCANDES             |

### Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | GE Current       |
| GTIN                      | 00043168737906   |
| Manufacturers Part Number | 300M/IF/130V-PK3 |
| UPC                       | 043168737906     |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | INCANDESCENT |
|----------------------|--------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 3    |
| Weight Per each | 0.22 |

### Uses, Certifications, and Standards

|             |          |
|-------------|----------|
| Application | STANDARD |
|-------------|----------|