



301042 Spliceline In-Line Wire Conn, 42 Orange, 100/Box

Ideal

Catalog Number	301042
Manufacturer	Ideal
Description	Ideal, Wire Connector, Spliceline, In-Line, Wire Size: 12 Awg - 20 Awg Solid, 12 Awg - 16 Awg Stranded, Color: Orange, Voltage Rating: 600 V, Amperage Rating: 20 Amp, Temperature Rating: 105 Deg C, Wire Type: Solid, Stranded, Model: 42
Weight per unit	0.0040 (lbs/each)
Product Category	Utp Connectors

Features

amperage rating	20
Voltage Rating	600
Wire Size	12 AWG - 20 AWG Solid, 12 AWG - 16 AWG Stranded
Wire Type	SOLID, STRANDED

Material, Color, and Finish

Color	Orange
-------	--------

Descriptions

Description	SPLICELINE IN-LINE WIRE CONN, 42 ORANGE, 100/BOX
extra long description	IDEAL 30-1042 SPLICELINE 42 ORANGE,
Features	A faster alternative to the butt splice. The SpliceLine In-Line Wire Connector is a revolutionary in-line wire connector that utilizes patented push-in technology in a unique design to provide a crimp-free, solderless butt splice faster and easier. The 2-port model supports a wide range of either stranded or solid wires, allowing one connector to cover the same range as three traditional butt splices and installs two times faster than a traditional butt splice. The end-to-end connection of SpliceLine is a gr
Long Description	IDEAL, Wire Connector, SpliceLine, In-Line, Wire Size: 12 AWG - 20 AWG Solid, 12 AWG - 16 AWG Stranded, Color: Orange, Voltage Rating: 600 V, Amperage Rating: 20 AMP, Temperature Rating: 105 DEG C, Wire Type: Solid, Stranded, Model: 42

Product Type	Spliceline 42 Orange, 100 Box
--------------	-------------------------------

Special Features	Features: Crimp-Free, Push-In Butt Splice; Low Insertion Force For Fast Connections; Easily Passes Through 1/2" Knockouts; End-To-End Connection Ideal For Pre-Fab Operations; Transparent Polycarbonate Window For Visual Inspection Of Connection; Wide Wire Range Of 12 - 20 Awg Solid, 12 - 16 Awg Stranded; Made In The U.S.A.; Model: 42
------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7929 N Sam Houston Pkwy W Suite 100
77064-0000, TX Houston
Phone: 281-345-1143
Fax: 281-345-7697

Manufacturer Information

Brand	Ideal
GTIN	00783250709090
Manufacturers Part Number	301042
UPC	783250709090

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	In-Line

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Package	1000
Weight Per each	0.004

Uses, Certifications, and Standards

Application	For Fast Connections And Pre-Fab Operations And Visual Inspection Of Connection
standard	CSA C22.2 #188, 486C/467 UL Listed, RoHS
Temperature Rating	105 DEG C