



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 301042 Spliceline In-Line Wire Conn, 42 Orange, 100/Box

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 301042  |
| Manufacturer     | Ideal   |
| Description      | Ideal, Wire Connector, Spliceline, In-Line, Wire Size: 12 Awg - 20 Awg Solid, 12 Awg - 16 Awg Stranded, Color: Orange, Voltage Rating: 600 V, Amperage Rating: 20 Amp, Temperature Rating: 105 Deg C, Wire Type: Solid, Stranded, Model: 42 |
| Weight per unit  | 0.0040 (lbs/each)   |
| Product Category | Utp Connectors  |

### Features

|                 |   |
|-----------------|---|
| amperage rating | 20  |
| Voltage Rating  | 600   |
| Wire Size       | 12 AWG - 20 AWG Solid, 12 AWG - 16 AWG Stranded |
| Wire Type       | SOLID, STRANDED                                 |

### Material, Color, and Finish

|       |        |
|-------|--------|
| Color | Orange |
|-------|--------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | SPLICELINE IN-LINE WIRE CONN, 42 ORANGE, 100/BOX  |
| extra long description | IDEAL 30-1042 SPLICELINE 42 ORANGE,   |
| Features               | A faster alternative to the butt splice.The SpliceLine In-Line Wire Connector is a revolutionary in-line wire connector that utilizes patented push-in technology in a unique design to provide a crimp-free, solderless butt splice faster and easier. The 2-port model supports a wide range of either stranded or solid wires, allowing one connector to cover the same range as three traditional butt splices and installs two times faster than a traditional butt splice.The end-to-end connection of SpliceLine is a gr |
| Long Description       | IDEAL, Wire Connector, SpliceLine, In-Line, Wire Size: 12 AWG - 20 AWG Solid, 12 AWG - 16 AWG Stranded, Color: Orange, Voltage Rating: 600 V, Amperage Rating: 20 AMP, Temperature Rating: 105 DEG C, Wire Type: Solid, Stranded, Model: 42   |
| Product Type           | Spliceline 42 Orange, 100 Box   |
| Special Features       | Features: Crimp-Free, Push-In Butt Splice; Low Insertion Force For Fast Connections; Easily Passes Through 1/2" Knockouts; End-To-End Connection Ideal For Pre-Fab Operations; Transparent Polycarbonate Window For Visual Inspection Of Connection; Wide Wire Range Of 12 - 20 Awg Solid, 12 - 16 Awg Stranded; Made In The U.S.A.; Model: 42  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250709090 |
| Manufacturers Part Number | 301042         |
| UPC                       | 783250709090   |

## Taxonomies, Classifications, and Categories

|                      |           |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type                 | In-Line   |

## Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Package         | 1000  |
| Weight Per each | 0.004 |

## Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| Application        | For Fast Connections And Pre-Fab Operations And Visual Inspection Of Connection |
| standard           | CSA C22.2 #188, 486C/467 UL Listed, RoHS  |
| Temperature Rating | 105 DEG C   |